

Features

- Halogen Free. "Green" Device (Note 1)
- Guard Ring Protection
- High Current Capability
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Lead Free Finish/RoHS Compliant (Note 2) ("P" Suffix Designates RoHS Compliant. See Ordering Information)


Maximum Ratings @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Value									Unit
		SS 12-L	SS 13-L	SS 14-L	SS 15-L	SS 16-L	SS 18-L	SS 110-L	SS 1150-L	SS 1200-L	
Peak Repetitive Reverse Voltage	V _{RRM}	20	30	40	50	60	80	100	150	200	V
Working Peak Reverse Voltage	V _{RWM}										
DC Blocking Voltage	V _R										
RMS Reverse Voltage	V _{RMS}	14	21	28	35	42	56	70	105	140	V
Average Rectified Forward Current	I _{F(AV)}	1									A
Non-Repetitive Peak Surge Current @ 8.3ms Half Sine Wave	I _{FSM}	30									A
Current Squared Time @1ms≤t≤8.3ms	I ² t	3.735									A ² s

Marking code

Part Number	Marking Code
SS12-L	SS12
SS13-L	SS13
SS14-L	SS14
SS15-L	SS15
SS16-L	SS16
SS18-L	SS18
SS110-L	SS110
SS1150-L	S1150
SS1200-L	S1200

Internal Structure


Pin	Description	Simplified Outline	Graphic Symbol
1	Cathode	 XXXX = Marking Code	
2	Anode		

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

2. High temperature solder exemption applied, see EU directive annex 7a.


1 Amp Surface Mount Schottky Rectifier 20 to 200 Volts

SMA (DO-214AC)



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.075	0.096	1.90	2.44	
B	0.050	0.064	1.27	1.63	
C	0.002	0.008	0.051	0.203	
D	---	0.020	---	0.51	
E	0.030	0.060	0.76	1.52	
F	0.065	0.091	1.65	2.32	
G	0.189	0.220	4.80	5.59	
H	0.157	0.187	4.00	4.75	
J	0.090	0.115	2.25	2.92	

SUGGESTED SOLDER PAD LAYOUT



Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
T_J	Operating Junction Temperature Range	SS12-L ~ SS14-L	-55		125	°C
T_J	Operating Junction Temperature Range	SS15-L ~ SS1200-L	-55		150	°C
T_{stg}	Storage Temperature Range		-55		150	°C
$R_{th(J-L)}$	Thermal Resistance from Junction to Lead	Note 1		22		°C/W
$R_{th(J-A)}$	Thermal Resistance from Junction to Ambient	Note 1		80		°C/W

Note:

1. Mounted on P.C.B. with 5mm*5mm copper pad areas.

Electrical Characteristics @ 25°C Unless Otherwise Specified

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage SS12-L ~ SS14-L SS15-L ~ SS16-L SS18-L ~ SS110-L SS1150-L SS1200-L	V_F	$I_F=1A; T_J=25^{\circ}C$			0.50 0.70 0.85 0.90 0.92	V
Reverse Current SS12-L ~ SS16-L SS18-L ~ SS1200-L	I_R	at Rated $V_R; T_J=25^{\circ}C$ at Rated $V_R; T_J=125^{\circ}C$ at Rated $V_R; T_J=25^{\circ}C$ at Rated $V_R; T_J=125^{\circ}C$			0.1 20 0.01 5	mA
Junction Capacitance SS12-L ~ SS14-L SS15-L ~ SS16-L SS18-L ~ SS110-L SS1150-L ~ SS1200-L	C_J	$V_R=4V; f=1MHz; T_J=25^{\circ}C$		50 40 30 20		pF

Curve Characteristics

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Forward Characteristics





Fig. 6 - Typical Reverse Leakage Characteristics



Curve Characteristics

Fig. 7 - Typical Forward Characteristics




Fig. 8 - Typical Reverse Leakage Characteristics




Fig. 9 - Typical Forward Characteristics




Fig. 10 - Typical Reverse Leakage Characteristics




Fig. 11 - Typical Capacitance Characteristics





Fig. 12 - Typical Capacitance Characteristics



Ordering Information

Device	Packing
SS12-LTP ~ SS1200-LTP	Tape&Reel:5Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.