

PTC/CAD

GLH

DRAWN

SEP 97

CHECK

REVISIONS

CHECK

1

ISSUE

M

CATALOG LISTING




LSQ310-20

PAGE 1 OF 1

REPLACES

PR-22895

RELEASE NO.



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION	
CHARACTERISTICS		SCALE FULL	
OPERATING TORQUE ----- 4 IN LBS MAX		DO NOT SCALE PRINT	
PRETRAVEL ----- 55°		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
CONTACT TRANSFER ----- 60°		ONE PLACE (.0) ±.030	
SEGMENT POSITION ----- 90°		TWO PLACE (.00) ±.015	
TOTAL SHAFT ROTATION ----- 360° CW OR CCW		THREE PLACE (.000) ±.005	
		ANGLES ±	
		WEIGHT	

NOTES

1 - SWITCH USES FLUOROSILICONE SEALS
IN OPERATING HEADS ONLY

ANSI Y14.5M-1982 APPLIES