


PBV CONNECTOR

2.0 mm pitch/Disconnectable Crimp style connectors



This PBV connector, which is mainly used for connecting PCB of flat television, is a crimping type connector and is designed to have a secure locking structure and a sucking area.

- Secure locking structure
- Sucking area on header
- High reliability contact

Specifications

- Current rating: 3 A AC/DC (AWG #22)
- Voltage rating: 100 V AC/DC
- Temperature range: -25°C to $+85^{\circ}\text{C}$
(including temperature rise in applying electrical current)
- Contact resistance: Initial value/ 10 m Ω max.
After environmental tests/ 20 m Ω max.
- Insulation resistance: Initial/ 1,000 M Ω min.
- Withstanding voltage: 800 VAC/minute
- Applicable wire: Conductor size/ AWG#28 to #22
Insulation O.D./ 0.9 to 1.5 mm
- * In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.


Standards

Recognized E 60389


PC board layout and Assembly layout

Top entry type

<2 circuits>




<3 to 15 circuits>




Side entry type

<2 circuits>



<3 to 15 circuits>




Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Tolerances are non-cumulative: ± 0.03 mm for all centers. The dimensions above should serve as a guideline. Contact JST for details.

PBV CONNECTOR

Contact



Model No.	Applicable wire		Insulation O.D. (mm)	Q'ty/reel
	mm ²	AWG #		
SPHD-001T-P0.5	0.13 to 0.33	26 to 22	1.0 to 1.5	8,000
SPHD-002T-P0.5	0.08 to 0.21	28 to 24	0.9 to 1.5	8,000

Material and Finish

Phosphor bronze, tin-plated (reflow treatment)


RoHS2 compliance

Contact	Crimping machine	Applicator		
		Crimp applicator	Dies	Crimp applicator with dies
SPHD-001T-P0.5	AP-K2N	MKS-L-10	MK/SPHD-001-05	APLMK SPHD001-05
SPHD-002T-P0.5			MK/SPHD-002-05	APLMK SPHD002-05


Note: Contact JST for fully automatic crimping applicator.

Housing


< 3 (2 circuits in common use) to 8 circuits >



< 9 to 12 circuits >



< 13 to 15 circuits >



No. of circuits	Model No.	Dimensions (mm)		Q'ty/ bag
		A	B	
*3	PBVP-03V-S	4.0	10.0	2,000
4	PBVP-04V-S	6.0	12.0	2,000
6	PBVP-06V-S	10.0	16.0	1,000
8	PBVP-08V-S	14.0	20.0	1,000
10	PBVP-10V-S	18.0	24.0	1,000
12	PBVP-12V-S	22.0	28.0	500
15	PBVP-15V-S	28.0	34.0	500

Material and Finish

PA 66, UL94V-0, natural (white)

RoHS2 compliance


Note*: 2 circuits in common use.

PBV CONNECTOR


Header

Top entry type


<2 circuits>




<3 to 8 circuits>



<9 to 12 circuits>




<13 to 15 circuits>




Side entry type


<2 circuits>




<3 to 8 circuits>



<9 to 12 circuits>



<13 to 15 circuits>



No. of circuits	Model No.		Dimensions (mm)		Q'ty/reel	
	Top entry type	Side entry type	A	B	Top type	Side type
*2	BM02(4.0)B-PBVSS-TF	SM02(4.0)B-PBVSS-TB	4.0	10.0	700	800
3	BM03B-PBVSS-TF	SM03B-PBVSS-TB	4.0	10.0	700	800
4	BM04B-PBVSS-TF	SM04B-PBVSS-TB	6.0	12.0	700	800
6	BM06B-PBVSS-TF	SM06B-PBVSS-TB	10.0	16.0	700	800
8	BM08B-PBVSS-TF	SM08B-PBVSS-TB	14.0	20.0	700	800
10	BM10B-PBVSS-TF	SM10B-PBVSS-TB	18.0	24.0	700	800
12	BM12B-PBVSS-TF	SM12B-PBVSS-TB	22.0	28.0	700	800
15	BM15B-PBVSS-TF	SM15B-PBVSS-TB	28.0	34.0	700	800

Material and Finish

Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

Wafer: Polyamide resin, UL94V-0, natural (ivory)

Reinforcement: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

RoHS2 compliance This product displays (LF)(SN) on a label.

Note: 1. These products listed above are supplied on embossed-tape.

2. *2 circuits product: Removing center pin from 3 circuits product

Model number allocation

Contact

S PHD - 002 T - P 0.5

Form: S...Strip form, B...Loose piece

Series name

Applicable wire range: 001...AWG #26 to AWG #22
002...AWG #28 to AWG #24

Surface finish: T...Tin-plated (reflow treatment)

Material: P...Phosphor bronze

Terminal size

Housing

PBV P - 03 V - S

Series name

Part name: Plug

No. of circuits: 3 to 15

Flammability: V...UL94V-0

Color: S...Natural (White)

Header

BM 03 B - PBV S S - TF

Shape of assembled product:
BM...SMT top entry type
SM...SMT side entry type

No. of circuits: 3 to 15
Only 2-circuit: BM02 (4.0) B-PBVSS-TF
SM02 (4.0) B-PBVSS-TB

Part name: Header

Series name

Color: S...Natural (Ivory)

Indication of clinch: S...Straight pin

Packaging style: TF...Embossed-taping (Top entry type)
TB...Embossed-taping (Side entry type)