











PRODUCT NUMBER SEE SHEET 2



SECTION Z-Z



spec ref				dr		Rainbow Zhan	2015/01/26		projection				size		A3		scale		3:2								
tolerance std				TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Rainbow Zhan		2015/02/11						ecn no		-							
ASME Y14.5								chr		-		-						rel level		Released							
								appr		Pei-Ming Zheng		2015/02/11						product family		PowerBlade+							
surface 				linear				title		6LP + 24S + 3HP VT STB RECEPTACLE				dwg no		10106268-3606001				rev		A					
																								0.X		±0.50	
																								0.XX		±0.25	
ASME Y14.5				angular		0°		±2°		www.fci.com				cat. no.				Product - Customer Drw				sheet 1 of 3					





Copyright FCI.

A


B

C

D

PRODUCT NO.	ROWS	HIGH POWER SIGNAL										LP						
		E1	P9	P8	P7	6	5	4	3	2	1	P6	P5	P4	P3	P2	P1	E2
10106268-360600ILF	D C B A		<div>H3</div>	<div>H3</div>	<div>H3</div>	<div>E</div> <div>E</div> <div>E</div> <div>E</div>	<div>E</div> <div>E</div> <div>E</div> <div>E</div>	<div>E</div> <div>E</div> <div>E</div> <div>E</div>	<div>E</div> <div>E</div> <div>E</div> <div>E</div>	<div>E</div> <div>E</div> <div>E</div> <div>E</div>	<div>E</div> <div>E</div> <div>E</div> <div>E</div>	<div>L</div> <div>R</div> <div>L</div> <div>R</div>	<div>L</div> <div>R</div> <div>L</div> <div>R</div>	<div>L</div> <div>R</div> <div>L</div> <div>R</div>	<div>L</div> <div>R</div> <div>L</div> <div>R</div>	<div>L</div> <div>R</div> <div>L</div> <div>R</div>	<div>L</div> <div>R</div> <div>L</div> <div>R</div>	

CODE	DESCRIPTION
E	STD SIGNAL CONTACT
H3	STD HIGH POWER CONTACT (3.43)
HA	METAL HOLD DOWN
LR	STD LOW POWER CONTACT (3.43)



dr	Rainbow Zhan	2015/01/26	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2		
eng	Rainbow Zhan	2015/02/11			ecn no	-				
chr	-	-			rel level	Released				
appr	Pei-Ming Zheng	2015/02/11	product family	PowerBlade+						
<div></div> <div>www.fci.com</div>	title	6LP + 24S + 3HP VT STB RECEPTACLE			dwg no	10106268-3606001			rev	A
cat. no.		Product - Customer Drw				sheet 2 of 3				

A




B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
 - HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
 - SIGNAL CONTACT - COPPER ALLOY.
 - POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- 9) THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL
MODULES AND END MODULES ARE OPTIONAL AND THE SHAPE
MAY BE DIFFERENT FOR OPTIMIZE THE MOLDING PROCESS. THE
VOID CORING WILL NOT EFFECT TO PRODUCT FUNCTION.

dr	Rainbow Zhan	2015/01/26	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	scale		
eng	Rainbow Zhan	2015/02/11			A3	1:1		
chr	-	-			ecn no -			
appr	Pei-Ming Zheng	2015/02/11	product family		PowerBlade+	rel level	Released	
	title	6LP + 24S + 3HP VT STB RECEPTACLE			dwg no	10106268-3606001	rev A	
www.fci.com		cat. no.	Product - Customer Drw			sheet 3 of 3		



Copyright FCI.