

Part Number : [2196751115](#)

Series Number : 219675

Status : Preliminary




Drawings

[2196751115_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:9325e1d8-af41-4cb1-9ff4-2f983cb1974c
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Preliminary
Category	Power and Signal Cable Assemblies
Series	219675
Description	Pre-Crimped Lead OneBlade Female-to-Pigtail, 1.00µm Tin (Sn) Plating, 450.00mm Length, 30 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	OneBlade Terminal-to-Pigtail
Keyword	Pre-Crimped Leads
Product Name	OneBlade
UPC	196823335709

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	0.449/g
Packaging Type	Bag
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Single Ended	Yes

Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10125
Wire Size (AWG)	30

Mates With / Use With

Use with Part(s)

Description	Part Number
OneBlade Single Row Receptacle Housings	<u>214092</u>

This document was generated on Dec 31, 2025