






Find out more about our products on:
www.amphenol-industrial.de



General Characteristics	Standard	Value
Type		hood
Protection class	IEC 60529	IP65 & IP66
Locking system	DIN EN 175 301-801 (DIN 43 652)	2 locking levers
Cable entry & position		M40 side
Climatical Characteristics	Standard	Value
Operating temperature	IEC 60068-1	-40°C - +100°C
Mechanical Characteristics	Standard	Value
Mechanical operation	IEC 60512-9-1	≥500 mating cycles
Materials	Value	
Housing material		Al (aluminium) alloy
Housing surface		powder coated
Housing color		grey (similar to RAL 9006)
Locking system material & surface		steel Zn-plated

Gewicht (errechnet) / Calc WT: 237,2 g				Zul. Abw./Tolerances:		Maßstab / Scale: 1:1 (1:2)		A3			
Prüfmaß / Testdimension				ISO 2768-m		 DIN / ISO 13715		CUSTOMER DRAWING			
Teileindex / Partindexnumber:											
Bagatelle change:						Tüllengehäuse E16 M40 <i>hood E16 M40</i>					
				Gez.	13.10.2016						
				Drawn	RSCHAEDEL						
				Status	Released						
				Gepr.	21.04.2021						
				Checked	MBERTSCH	M C146 21R016 503 8					
Amphenol Tuchel Industrial GmbH											
02	202100101	01.10.2021	PWÖLF								
01	201600001	13.10.2016	RSCHAEDEL	Blatt / Sheet 1							
Index Änderun				Description		Datum / Date		Name		Ers. f. / Replacement for:	
										1 Bl.	