

# High Efficiency Thyristor


$$\begin{aligned} V_{RRM} &= 1200 \text{ V} \\ I_{TAV} &= 30 \text{ A} \\ V_T &= 1.27 \text{ V} \end{aligned}$$

Two Quadrants Operation QI & QII  
 Single Thyristor with two gate polarities



Part number

**CLA30E1200NPZ**

Marking on Product: CLA30E1200NPZ



Backside: anode



## Features / Advantages:

- Thyristor for line frequency
- Planar passivated chip
- Long-term stability
- Two gate current polarities usable
  - positive -> quadrant I
  - negative -> quadrant II
- Thyristor can be used as Triac
  - anti-parallel combination with AGT
  - Anode-Gated-Thyristor covers quadrant III
  - AGT-counterpart: CLB30I1200PZ

## Applications:

- Line rectifying 50/60 Hz
- Softstart AC motor control
- DC Motor control
- Power converter
- AC power control
- Lighting and temperature control

## Package: TO-263 (D2Pak-HV)

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0


## Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).

| Thyristor      |                                                      |                                                                                                                                                                                                       |                                | Ratings |      |          |                  |
|----------------|------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|---------|------|----------|------------------|
| Symbol         | Definition                                           | Conditions                                                                                                                                                                                            |                                | min.    | typ. | max.     | Unit             |
| $V_{RSM/DSM}$  | max. non-repetitive reverse/forward blocking voltage | $T_{VJ} = 25^{\circ}\text{C}$                                                                                                                                                                         |                                |         |      | 1300     | V                |
| $V_{RRM/DRM}$  | max. repetitive reverse/forward blocking voltage     | $T_{VJ} = 25^{\circ}\text{C}$                                                                                                                                                                         |                                |         |      | 1200     | V                |
| $I_{R/D}$      | reverse current, drain current                       | $V_{R/D} = 1200\text{ V}$                                                                                                                                                                             | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 10       | $\mu\text{A}$    |
|                |                                                      | $V_{R/D} = 1200\text{ V}$                                                                                                                                                                             | $T_{VJ} = 125^{\circ}\text{C}$ |         |      | 2        | mA               |
| $V_T$          | forward voltage drop                                 | $I_T = 30\text{ A}$                                                                                                                                                                                   | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 1.30     | V                |
|                |                                                      | $I_T = 60\text{ A}$                                                                                                                                                                                   |                                |         |      | 1.59     | V                |
|                |                                                      | $I_T = 30\text{ A}$                                                                                                                                                                                   | $T_{VJ} = 125^{\circ}\text{C}$ |         |      | 1.27     | V                |
|                |                                                      | $I_T = 60\text{ A}$                                                                                                                                                                                   |                                |         |      | 1.65     | V                |
| $I_{TAV}$      | average forward current                              | $T_C = 115^{\circ}\text{C}$                                                                                                                                                                           | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 30       | A                |
| $I_{T(RMS)}$   | RMS forward current                                  | 180° sine                                                                                                                                                                                             |                                |         |      | 47       | A                |
| $V_{T0}$       | threshold voltage                                    | } for power loss calculation only                                                                                                                                                                     | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 0.86     | V                |
| $r_T$          | slope resistance                                     |                                                                                                                                                                                                       |                                |         |      | 13.2     | m $\Omega$       |
| $R_{thJC}$     | thermal resistance junction to case                  |                                                                                                                                                                                                       |                                |         |      | 0.5      | K/W              |
| $R_{thCH}$     | thermal resistance case to heatsink                  |                                                                                                                                                                                                       |                                |         | 0.25 |          | K/W              |
| $P_{tot}$      | total power dissipation                              |                                                                                                                                                                                                       | $T_C = 25^{\circ}\text{C}$     |         |      | 250      | W                |
| $I_{TSM}$      | max. forward surge current                           | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$                                                                                                                                                      | $T_{VJ} = 45^{\circ}\text{C}$  |         |      | 300      | A                |
|                |                                                      | $t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$                                                                                                                                                     | $V_R = 0\text{ V}$             |         |      | 325      | A                |
|                |                                                      | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$                                                                                                                                                      | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 255      | A                |
|                |                                                      | $t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$                                                                                                                                                     | $V_R = 0\text{ V}$             |         |      | 275      | A                |
| $I^2t$         | value for fusing                                     | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$                                                                                                                                                      | $T_{VJ} = 45^{\circ}\text{C}$  |         |      | 450      | A <sup>2</sup> s |
|                |                                                      | $t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$                                                                                                                                                     | $V_R = 0\text{ V}$             |         |      | 440      | A <sup>2</sup> s |
|                |                                                      | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$                                                                                                                                                      | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 325      | A <sup>2</sup> s |
|                |                                                      | $t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$                                                                                                                                                     | $V_R = 0\text{ V}$             |         |      | 315      | A <sup>2</sup> s |
| $C_J$          | junction capacitance                                 | $V_R = 400\text{ V}$ $f = 1\text{ MHz}$                                                                                                                                                               | $T_{VJ} = 25^{\circ}\text{C}$  |         | 13   |          | pF               |
| $P_{GM}$       | max. gate power dissipation                          | $t_p = 30\text{ }\mu\text{s}$                                                                                                                                                                         | $T_C = 150^{\circ}\text{C}$    |         |      | 10       | W                |
|                |                                                      | $t_p = 300\text{ }\mu\text{s}$                                                                                                                                                                        |                                |         |      | 5        | W                |
| $P_{GAV}$      | average gate power dissipation                       |                                                                                                                                                                                                       |                                |         |      | 0.5      | W                |
| $(di/dt)_{cr}$ | critical rate of rise of current                     | $T_{VJ} = 150^{\circ}\text{C}; f = 50\text{ Hz}$ repetitive, $I_T = 90\text{ A}$                                                                                                                      |                                |         |      | 150      | A/ $\mu\text{s}$ |
|                |                                                      | $t_p = 200\text{ }\mu\text{s}; di_G/dt = 0.3\text{ A}/\mu\text{s};$<br>$I_G = 0.3\text{ A}; V = \frac{2}{3} V_{DRM}$ non-repet., $I_T = 30\text{ A}$                                                  |                                |         |      | 500      | A/ $\mu\text{s}$ |
| $(dv/dt)_{cr}$ | critical rate of rise of voltage                     | $V = \frac{2}{3} V_{DRM}$                                                                                                                                                                             | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 500      | V/ $\mu\text{s}$ |
|                |                                                      | $R_{GK} = \infty$ ; method 1 (linear voltage rise)                                                                                                                                                    |                                |         |      |          |                  |
| $V_{GT}$       | gate trigger voltage                                 | $V_D = 6\text{ V}$                                                                                                                                                                                    | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 1.3      | V                |
|                |                                                      |                                                                                                                                                                                                       | $T_{VJ} = -40^{\circ}\text{C}$ |         |      | 1.6      | V                |
| $I_{GT}$       | gate trigger current                                 | $V_D = 6\text{ V}$                                                                                                                                                                                    | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | $\pm 30$ | mA               |
|                |                                                      |                                                                                                                                                                                                       | $T_{VJ} = -40^{\circ}\text{C}$ |         |      | $\pm 50$ | mA               |
| $V_{GD}$       | gate non-trigger voltage                             | $V_D = \frac{2}{3} V_{DRM}$                                                                                                                                                                           | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 0.2      | V                |
| $I_{GD}$       | gate non-trigger current                             |                                                                                                                                                                                                       |                                |         |      | $\pm 1$  | mA               |
| $I_L$          | latching current                                     | $t_p = 10\text{ }\mu\text{s}$                                                                                                                                                                         | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 90       | mA               |
|                |                                                      | $I_G = 0.3\text{ A}; di_G/dt = 0.3\text{ A}/\mu\text{s}$                                                                                                                                              |                                |         |      |          |                  |
| $I_H$          | holding current                                      | $V_D = 6\text{ V}$ $R_{GK} = \infty$                                                                                                                                                                  | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 60       | mA               |
| $t_{gd}$       | gate controlled delay time                           | $V_D = \frac{1}{2} V_{DRM}$                                                                                                                                                                           | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 2        | $\mu\text{s}$    |
|                |                                                      | $I_G = 0.3\text{ A}; di_G/dt = 0.3\text{ A}/\mu\text{s}$                                                                                                                                              |                                |         |      |          |                  |
| $t_q$          | turn-off time                                        | $V_R = 100\text{ V}; I_T = 30\text{ A}; V = \frac{2}{3} V_{DRM}$ $T_{VJ} = 125^{\circ}\text{C}$<br>$di/dt = 10\text{ A}/\mu\text{s}$ $dv/dt = 20\text{ V}/\mu\text{s}$ $t_p = 200\text{ }\mu\text{s}$ |                                |         | 150  |          | $\mu\text{s}$    |

| Package TO-263 (D2Pak-HV) |                                                              |                      | Ratings |      |      |      |
|---------------------------|--------------------------------------------------------------|----------------------|---------|------|------|------|
| Symbol                    | Definition                                                   | Conditions           | min.    | typ. | max. | Unit |
| $I_{RMS}$                 | RMS current                                                  | per terminal         |         |      | 35   | A    |
| $T_{VJ}$                  | virtual junction temperature                                 |                      | -40     |      | 150  | °C   |
| $T_{op}$                  | operation temperature                                        |                      | -40     |      | 125  | °C   |
| $T_{stg}$                 | storage temperature                                          |                      | -40     |      | 150  | °C   |
| <b>Weight</b>             |                                                              |                      |         | 1.5  |      | g    |
| $F_C$                     | mounting force with clip                                     |                      | 20      |      | 60   | N    |
| $d_{Spp/App}$             | creepage distance on surface / striking distance through air | terminal to terminal | 4.2     |      |      | mm   |
| $d_{Spb/Apb}$             |                                                              | terminal to backside | 4.7     |      |      | mm   |

### Product Marking



### Part description


C = Thyristor (SCR)  
 L = High Efficiency Thyristor  
 A = (up to 1200V)  
 30 = Current Rating [A]  
 E = Single Thyristor with two gate polarities  
 1200 = Reverse Voltage [V]  
 N = Three Quadrants operation: QI - QIII  
 PZ = TO-263AB (D2Pak) (2HV)

| Ordering    | Ordering Number   | Marking on Product | Delivery Mode | Quantity | Code No. |
|-------------|-------------------|--------------------|---------------|----------|----------|
| Standard    | CLA30E1200NPZ-TRL | CLA30E1200NPZ      | Tape & Reel   | 800      | 516330   |
| Alternative | CLA30E1200NPZ-TUB | CLA30E1200NPZ      | Tube          | 50       | 525248   |

### Equivalent Circuits for Simulation


\* on die level

$T_{VJ} = 150^{\circ}\text{C}$




Thyristor

|             |                    |      |    |
|-------------|--------------------|------|----|
| $V_{0\max}$ | threshold voltage  | 0.86 | V  |
| $R_{0\max}$ | slope resistance * | 10   | mΩ |

**Outlines TO-263 (D2Pak-HV)**


| Dim. | Millimeter |       | Inches      |       |
|------|------------|-------|-------------|-------|
|      | min        | max   | min         | max   |
| A    | 4.06       | 4.83  | 0.160       | 0.190 |
| A1   | typ. 0.10  |       | typ. 0.004  |       |
| A2   | 2.41       |       | 0.095       |       |
| b    | 0.51       | 0.99  | 0.020       | 0.039 |
| b2   | 1.14       | 1.40  | 0.045       | 0.055 |
| c    | 0.40       | 0.74  | 0.016       | 0.029 |
| c2   | 1.14       | 1.40  | 0.045       | 0.055 |
| D    | 8.38       | 9.40  | 0.330       | 0.370 |
| D1   | 8.00       | 8.89  | 0.315       | 0.350 |
| D2   | 2.3        |       | 0.091       |       |
| E    | 9.65       | 10.41 | 0.380       | 0.410 |
| E1   | 6.22       | 8.50  | 0.245       | 0.335 |
| e    | 2,54 BSC   |       | 0,100 BSC   |       |
| e1   | 4.28       |       | 0.169       |       |
| H    | 14.61      | 15.88 | 0.575       | 0.625 |
| L    | 1.78       | 2.79  | 0.070       | 0.110 |
| L1   | 1.02       | 1.68  | 0.040       | 0.066 |
| W    | typ. 0.02  | 0.040 | typ. 0.0008 | 0.002 |

All dimensions conform with and/or within JEDEC standard.



## Thyristor




Fig. 1 Forward characteristics




Fig. 2 Surge overload current  
 $I_{TSM}$ : crest value,  $t$ : duration




Fig. 3  $I^2t$  versus time (1-10 s)




Fig. 4 Gate voltage & gate current  
 Triggering: A = no; B = possible; C = safe




Fig. 5 Gate controlled delay time  $t_{gd}$




Fig. 6 Max. forward current at case temperature




Fig. 7a Power dissipation versus direct output current  
 Fig. 7b and ambient temperature




Fig. 7 Transient thermal impedance junction to case