Part Number : 638114200
Product Description : PremiumGrade Hand Crimp Tool for 2.54mm MX64 Terminals, 22-18 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-6381142HM-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per ED/61/2018

Downloaded from Arrow.com.

	(27 June 2018)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for 2.54mm MX64 Terminals, 22-18 AWG
Comments	Prototype and field repair; Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054736920
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when

Downloaded from Arrow.com.

	used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	428.885/g

Applicable Parts

Description	Part Number
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 22 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	334670003
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 22 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing	334670004
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 20-18 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	334670005
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 20-18 AWG, Left Reel Payoff, Also used with	334670006

Downloaded from Arrow.com.

MX123 Female Receptacle Housing	
2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 22 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	334680001
2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 22 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing	334680002
2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 20-18 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	334680003
2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 20-18 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing	334680004
2.54mm Pitch MX64 Terminal, Silver Plating, 22 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing	347361001
2.54mm Pitch MX64 Terminal, Silver Plating, 20-18 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing	347361002
2.54mm Pitch MX64 Terminal, Silver Plating, 22 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	347362001
2.54mm Pitch MX64 Terminal, Silver Plating, 20-18 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	347362002

Downloaded from Arrow.com.