

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, without Sides and Doors, Black, 1991H x 750W x 1200D mm

AR3350X617

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters

Physical

Height	199.1 cm
Width	75 cm
Depth	120 cm
Product weight	161.36 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	104.8 cm
minimum mounting depth	26.19 cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge post 18 gauge roof
Permanent permissible load	1020.6 kg dynamic 1360.8 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	211.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	133.4 cm
Package 1 Length	85.1 cm
Package 1 Weight	183.18 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained](#) >

[How we assess product sustainability](#) >

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes

Image of product / Alternate images

Alternative

