

Housing - HC-STA-D15-HLFS-1TTM20-ELC-AL - 1424350

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing D15, for single locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 1, straight, Height: 56 mm, Cable gland: none, Gland: no, 1x M20, Standard

RoHS

Key Commercial Data

Packing unit	1
GTIN	 4 055626 370866
GTIN	4055626370866
Custom tariff number	85472000

Technical data

Dimensions

Height	56 mm
Width	30 mm
Length	63.5 mm

Ambient conditions

Degree of protection of housing (IP)	IP66
	IP67
Degree of protection of housing (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D15, A10
------	---------------------------------

Housing - HC-STA-D15-HLFS-1TTM20-ELC-AL - 1424350


Technical data

General

Size	D15
Housing type	Sleeve housing
Color	silver
Locking type	for single locking latch
No. of cable outlets	1
Cable exit	straight
Screw connection	none
Type of the screw connection	1x M20
Housing material	Die-cast aluminum, salt water resistant
Seal material	NBR

Drawings

Dimensional drawing



Dimensional drawing