Part Number : 1200860338
Product Description : Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length
Series Number : 120086
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 403000K05M020



Documents and Resources

Drawings

1200860338_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	78678854290

Agency

UL	E152210

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	4.95mm (.195")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPE

Downloaded from Arrow.com.

Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	255.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	22

Downloaded from Arrow.com.