


© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECR-23-175974	20OCT2023	MV	JP








SECTION A–A
SCALE 20:1

1. 0.00076 [.000030] MIN GOLD PER IN LOCALIZED GOLD PLATE AREA AND 0.00254–0.00635 [.000100–.000250] BRIGHT TIN–LEAD PER IN LOCALIZED TIN–LEAD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.

2. WIRE RANGE: 0.5–1.4MM^2 (20–16 AWG).

3. INSULATION RANGE: 2.01–3.20[.079–.126] DIA.

4. 0.00076 [.000030] MIN GOLD PER IN LOCALIZED GOLD PLATE AREA AND 0.00254–0.00635 [.000100–.000250] MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.



SECTION B–B
SCALE 20:1

PART NUMBER	MATERIAL	FINISH
1–794407–1	0.25 [.010] PH BRZ	4
1–794407–0	0.25 [.010] BRASS	4
~~794407–6~~	0.25 [.010] PHOS BRONZE	1
794407–4	0.25 [.010] PHOS BRONZE	PRE–TIN
794407–3	0.25 [.010] BRASS	1
794407–1	0.25 [.010] BRASS	PRE–TIN

SUPERCEDED BY 1–794407–1

SUPERCEDED BY 1–794407–0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13[.005]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –

FINISH –

DWN S. HOOVER 10JAN03
CHK C.JONES 10JAN03
APVD C.JONES 10JAN03
PRODUCT SPEC 108–1542
APPLICATION SPEC 114–16017
WEIGHT 0.000000

TE Connectivity

NAME
SOCKET,
MINI UNVIVERSAL MATE–N–LOK(TM)
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C–794407	–

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV G2

794407

1471–9 (1/15)

Downloaded from Arrow.com.