Part Number : 330014022
Product Description : MX150 Female Terminal for Unsealed Connectors, Silver Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.
Series Number : 33001
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

330014022_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-33012-002-001.pdf

AS-33012-002-CH-001.pdf

PS-33012-002-001.pdf

TS-33001-003-001.pdf

TS-33001-004-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	33001
Description	MX150 Female Terminal for Unsealed Connectors, Silver Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Comments	Right Reel Payoff, Small Polarization Rib; For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers; Not to be used with MX150 Sealed Connectors
Product Name	MX150
UPC	822350753685

Electrical

Current - Maximum per Contact	Contact Molex

Downloaded from Arrow.com.

Voltage - Maximum	14V DC

Physical

Gender	Female
Grip Code	18
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	0.443/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.54mm max.
Wire Size (AWG)	18, 20
Wire Size mm^2	0.75-1.00

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	33472
MX150 Mat-Sealed Single Row Female Connector Assemblies	33471

Application Tooling

Global

Description	Part Number
Extraction Toolkit for MX150 Connectors	2002220700

Downloaded from Arrow.com.

PremiumGrade Hand Crimp Tool for MX150 Female Terminals, 22-18 AWG	638116000
PremiumGrade Hand Crimp Tool for MX150 Female Terminals for 1.00mm² and 1.50mm² Metric Wires	638116100
Hand Crimp Tool Metric 0.5 and 0.75	638116200
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	638131500
ServiceGrade Hand Crimp Tool for MX150 Crimp Terminals, 22-14 AWG	640160133

Downloaded from Arrow.com.