




Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Photocells



Product Availability: **Americas**
Street Lighting Photo Control Technology: **Electronic**
Operating Voltage Range: **105 – 305 VAC**
Grade: **Commercial**
Load Rating (Ballast): **1800 VA**

Features

Configuration Features

Number of Positions	3
---------------------	---

Industry Standards

Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	ANSI C136.24

Body Features

Lead Length	193.04 mm[7.6 in]
Primary Product Color	Black

Dimensions

MOV Diameter	20 mm
Wire Size	16 AWG
Product Length	58.5 mm[2.3 in]
Product Width	33 mm[1.29 in]

Product Availability

Product Availability	Americas
----------------------	----------



Product Type Features

Street Lighting Photo Control Technology	Electronic
--	------------

Electrical Characteristics

Operating Voltage Range	105 – 305 VAC
Load Rating (Ballast)	1800 VA
Load Rating (Tungsten)	1000 W
Fail Mode	On
Surge Protection	445 Joule
Operating Frequency	50 – 60 Hz
Relay Rating	30A General Purpose

Other

Grade	Commercial
OFF/ON Ratio	1.5:1
EU RoHS Compliance	Compliant

Mechanical Attachment

Mounting Options	Fixed Mount
------------------	-------------

Operation/Application

Turn OFF Time Delay	2 – 5 seconds
Turn ON Light Level	1.5 fc
Turn ON Time Delay	Instant On seconds

Usage Conditions

Operating Temperature Range	-40 – 70 °C[-40 – 158 °F]
-----------------------------	---------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2324697-2
PUSH GRIP CONNECTOR 2P



TE Part # 2324697-5
PUSH GRIP CONNECTOR 5P



TE Part # 2324697-6
PUSH GRIP CONNECTOR 6P




TE Part # 2324697-4
PUSH GRIP CONNECTOR 4P



TE Part # 2324697-3
PUSH GRIP CONNECTOR 3P

Also in the Series | ALR AA



Street Lighting Photocells(9)

Customers Also Bought





TE Part #2213362-2

Rcpt Assy, Dimmable Photocontrol, 150C, 3/4



TE Part #1-2834074-3

3P PLUG, MINIATURE WATERPROOF CONN, WHITE



TE Part #1-2834075-3

3P REC, MINIATURE WATERPROOF CONN, WHITE



TE Part #1-1393243-5

RTE24524



TE Part #794272-1

03P UMNL WIRE SEAL



TE Part #454100-000

D-406-0002



TE Part #967398-000

D-406-0001




TE Part #170014-5

FF 110 TAB 20-16AWG BR



TE Part #2361116-1

LUMAWISE Endurance N+ Shorting Cap



TE Part #117981-000

DS-14-16-RS

Documents

Product Drawings

ALR-AA-2000EL Photocontrol

English

CAD Files

Customer View Model

ENG_CVM_CVM_2393866-1_1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2393866-1_1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2393866-1_1.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



LUMAWISE ALR AA Series

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English