




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER *	WEIGHT lbs/100 pcs (g)/100 pcs	MAXIMUM BUNDLE CAPACITY	PANEL DIMENSIONS	
			THICKNESS	HOLE SIZE
VWS106----	0.397 (180)	1.06 (26.9)	UP TO 0.090 (UP TO 2.29)	0.187 (4.76)



- NOTES:
- * 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
 - 2. -20 MATERIAL DESIGNATION IS PIGMENTED BLACK



DIMENSIONS IN BRACKETS ARE METRIC [mm]
CAD FILENAME/LAYERS G01332BB_PB_VWS106_03

PANDUIT CORP. TINLEY PARK, ILLINOIS

VWS106-
VERTICAL WIRE SADDLE

3	7-03-01	LGG		UPDATED AND ADDED REF	G01332BB	3			
2	4-21-98	MLD		DIM 0.34 (8.6) WAS 0.36 (9.1)	G01332BB	2			
1	7-29-97	JAD		MAX PANEL THICKNESS CHANGED FROM .105 TO .090. ADDED 1.18 DIM, ADDED 'INSTALLED' TO 1.3 DIM.	G01332BB	1			
R	7-24-97	JAD		INITIAL RELEASE	G01332BB	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JAD	MAT'L: NYLON 6/6	SCALE NONE	DWG A
DATE 7-24-97		DRAWING NO. GB1332BB	SIZE
CHK'D			