

EAO – Your Expert Partner for Human Machine Interfaces

10-2J06.3146 - Single-LED

10-2J06.3146 - Single-LED



Attention: The preview is based on a sample product. This can differ from your current configuration.

Attribute


Dom. Wavelength	470 nm
Illumination colour	Blue
Lumi. Intensity 1 value	680 mcd
Lumi. Intensity	680 mcd
Operation current	15 mA $\pm$ 15 %
Operating voltage	6 V DC +10%
Operating Voltage/Current	6 V +10% 15 mA $\pm$ 15 %
Socket	T1 ¾ MG
Weight	0.002 kg

EAO – Your Expert Partner for Human Machine Interfaces

10-2J06.3146 - Single-LED

Wiring diagrams

x2+



x1-

Additional information

Due to high surface temperatures, the series resistor must not be soldered directly to the terminals of the equipment (use a terminal plate)

When using AC/DC types with AC operation, slight flickering can occur

The luminous intensity stated is for when used with DC

Electrical and optical data are measured at 25 °C

The specified versions are built with a protection diode (half wave rectifier) in series and the LED

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

Where supply voltages are over 48 V, a voltage-reduction element (external protective series resistor) must be used.

Keep to the country specific safety instructions