

	Production (NRND)
Product Status	Recommended Alternate Part No. : TFM201610ALMAR47MTAA (Interchangeability is not guaranteed.)
Applications	Automotive Grade
Feature	Wire WoundWire Wound ShieldMagnetic Shield Ferrite CoreFerrite Core
Series Type	VLS-E
Brand	TDK
Environmental Compliance	RoHS REACH Halogen Free Lead Free



Size	
Length(L)	2.00mm ±0.10mm
Width(W)	1.60mm ±0.10mm
Thickness Height	0.95mm Max.
Recommended Land Pattern (A)	0.65mm Nom.
Recommended Land Pattern (B)	0.70mm Nom.
Recommended Land Pattern (C)	1.60mm Nom.

Electrical Characteristics	
Inductance	470nH ±30% at 1MHz
Rated Current (L Change) [Typ.]	2.1A (30% Down)
Rated Current (L Change) [Max.]	1.85A (30% Down)
Rated Current (Temperature Rise) [Typ.]	1.95A (40°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	54mΩ
DC Resistance [Max.]	65mΩ
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other	
Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
Soldering Method	Reflow
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]







! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.


! All specifications are subject to change without notice.

Package Quantity	2000pcs
Weight	0.012g

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



Associated Images

