



726 ET SERIES MAGNETIC CIRCUIT




C1 = 1000pF, 2KV CAPACITOR


R1-R4 = 75 OHMS, 1/16 W RESISTORS



PIN DESIGNATION



SUGGESTED PCB LAYOUT
(Component Side)

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN G. ATTADIA — 17MAR2005		DONGGUAN CHINA
			CHK D. FAROLE — 17MAR2005		
			APVD D. FAROLE — 17MAR2005		
			MODEL NAME		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:			DESC	
	0 PLC	±	—	MAGJACK GANG	1X2 726ET 10/100 TAB UP W/ LED
	1 PLC	±	—		
	2 PLC	±	.010		
	3 PLC	±	.005		
	4 PLC	±	—		
	ANGLES	±	—		
PRODUCT SPEC 108-2100	APPLICATION SPEC —			NON-POE	
				SIZE A1	
				CAGE CODE C=6610197	
				DRAWING NO —	RESTRICTED TO —
			CUSTOMER DRAWING		
				SCALE NTS	
				SHEET 2	OF 2
				REV D	