




D

C

B


A



REAR VIEW

DRAWING REVISIONS (RELEASE DATE ON FILE)			
REV	DOCUMENT	APP	APPROVAL DATE
E	PER CO# 839	V.R.	01/18/10

2.6 REF
[0.10]
SECONDARY LOCKS SHIPPED
IN PRE-STAGED POSITION



- NOTES:
- DIMENSIONS SHOWN IN MILLIMETERS [INCHES].
 - FOR WIRE SIZE APPLICATIONS, CONSULT FACTORY.
 - FEMALE TERMINALS TO BE ORDERED SEPARATELY: P/N'S 425 00 00 873/872.
 - PART MATES WITH CINCH HEADER CONNECTOR (CONSULT FACTORY).
 - SEAL PLUGS TO BE ORDERED SEPARATELY: P/N 581 00 00 011.
 - DRAWING TOLERANCES (UNLESS OTHERWISE SPECIFIED):
.X = ±0.5
.XX = ±0.25
 - SEALING RANGE FOR WIRE INSULATION DIAMETER:
MAXIMUM: 2.64MM [0.104"]; MINIMUM: 1.96MM [0.077"].
 - A TRIANGLE "▲" INDICATES A CHARACTERISTIC REQUIRING INSPECTION VERIFICATION.
 - IF TIE-WRAP DRESSING CONDUCTORS, CINCH RECOMMENDS A SPACING OF NO LESS THAN 50.8MM [2.00"] BEHIND THE BACK PLATE.

UNITS
METRIC

DESIGN ENGINEER
A.CAINES

DATE
4/25/00

PRO/E

CINCH

1700 FINLEY RD
LOMBARD, IL 60148

MODELED BY:

DO NOT SCALE DRAWING

UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS ARE IN mm

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH.
NEITHER THIS DOCUMENT NOR ANY OF
THE INFORMATION CONTAINED IN IT MAY
BE DUPLICATED OR DISCLOSED WITHOUT
PRIOR WRITTEN CONSENT OF CINCH.
©COPYRIGHT 2009 CINCH

APPROVALS
ON FILE

TITLE
18 POSITION SOCKET CONNECTOR

MATERIAL

MATERIAL SPEC NUMBER

CAD FILE NUMBER
5810118023

CAGE IDENT NO.
71785

FINISH

CONTROL SPEC NUMBER

PROJECT NUMBER
A14243

DRAWING NUMBER
5810118023S

SIZE
B

SCALE
1.500

SHEET 1 OF 1