


**H2,5/14DS BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
Material: E-Cu, tin galvanised  
Dimensional tolerance acc. to DIN 46228 sect. 4

**General ordering data**

|            |                                               |
|------------|-----------------------------------------------|
| Version    | Wire-end ferrule, Standard, 10 mm, 8 mm, blue |
| Order No.  | <a href="#">1333100000</a>                    |
| Type       | H2,5/14DS BL                                  |
| GTIN (EAN) | 4008190160364                                 |
| Qty.       | 500 items                                     |
| Packaging  | loose                                         |

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

### Dimensions and weights

Net weight 0.13 g

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

### Technical data

| Description of article | Wire end ferrule with plastic collar, special size, blue | Version | Standard |
|------------------------|----------------------------------------------------------|---------|----------|
|------------------------|----------------------------------------------------------|---------|----------|

### Wire-end ferrules

|                               |                     |                                         |             |
|-------------------------------|---------------------|-----------------------------------------|-------------|
| Contact surface diameter (D1) | 2.2 mm              | Contact surface length (L2)             | 8 mm        |
| Collar diameter (D2)          | 4 mm                | Plastic collar thickness (S2)           | 0.25 mm     |
| L1 in mm                      | 14.00 mm            | Wire connection cross section AWG, max. | AWG 14      |
| Metal sleeve thickness (S1)   | 0.15 mm             | Stripping length                        | 10 mm       |
| Conductor cross-section       | 2.5 mm <sup>2</sup> | Colour code                             | Weidmueller |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

Drawing

