

| REV.         | DESIGN | MATERIAL   | SURFACE  | WIRE RANGE           | INSULATION   | WIRE CRIMP                                  | INSUL. CRIMP                  | A   | B   | C   | D    | E   |
|--------------|--------|------------|--|----------------------|--------------|---|-------------------------------|-----|-----|-----|------|-----|
| 2386386-9    | A      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 2386386-6    | A      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 2386386-3    | A      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 2386386-1    | A      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 2367105-6    | A      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.35-0.5 FLR/FLU     | 1.2-1.4      | E = 2.4<br>G = 2.3<br>D <sub>Dr</sub> = 1.0 | H = 2.9<br>K = 2.9<br>D = 1.4 | 2.5 | 3.8 | 5.7 | 18.8 | 0.2 |
| 2367105-3    | A      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.35-0.5 FLR/FLU     | 1.2-1.4      | E = 2.4<br>G = 2.3<br>D <sub>Dr</sub> = 1.0 | H = 2.9<br>K = 2.9<br>D = 1.4 | 2.5 | 3.8 | 5.7 | 18.8 | 0.2 |
| 2367105-1    | A      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.35-0.5 FLR/FLU     | 1.2-1.4      | E = 2.4<br>G = 2.3<br>D <sub>Dr</sub> = 1.0 | H = 2.9<br>K = 2.9<br>D = 1.4 | 2.5 | 3.8 | 5.7 | 18.8 | 0.2 |
| 965901-1     | A      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLR          | 1.4-2.3      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 965899-1     | A      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 928876-1     | A      | CuSn4      | PLAIN BLANK  | 0.5-1.0 FLK          | 2.0-2.7      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.9<br>K = 4.1<br>D = 2.4 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927775-7     | M      | CuNi12Zn24 | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLK          | 2.0-2.7      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.9<br>K = 4.1<br>D = 2.4 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927775-6     | M      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLK          | 2.0-2.7      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.9<br>K = 4.1<br>D = 2.4 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927775-3     | M      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLK          | 2.0-2.7      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.9<br>K = 4.1<br>D = 2.4 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927775-1     | M      | CuFe2      | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLK          | 2.0-2.7      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.9<br>K = 4.1<br>D = 2.4 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 928810-1     | A      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.3      | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3.0 | 4.0 | 5.5 | 18.8 | 0.4 |
| 963884-1     | A      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.0-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 927773-3     | N      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 2.7-4.1      | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.5<br>K = 5.8<br>D = 3.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 927773-1     | N      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 2.7-4.1      | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.5<br>K = 5.8<br>D = 3.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 2-927768-1   | R      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 1-927768-1   | R      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| A19 927768-9 | P      | CuSn4      | PRET INNED vorverzinkt min. 1µm Spring selective Au Plated | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 927768-8     | P      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 927768-6     | P      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 927768-3     | P      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 927768-1     | P      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLR          | 2.1-3.1 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 4.7<br>K = 4.9<br>D = 2.6 | 3.3 | 4.3 | 5.8 | 18.8 | 0.4 |
| 1719810-1    | A      | CuSn4      | PLAIN BLANK  | 0.08-0.2 AWG/Special | 1.5-1.8      | E = 1.7<br>G = 1.7<br>D <sub>Dr</sub> = 0.6 | H = 3.1<br>K = 3.2<br>D = 1.6 | 2.5 | 3.7 | 5.9 | 18.8 | 0.4 |
| 2-927771-2   | N      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLR          | 1.4-2.3 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 2-927771-1   | N      | CuFe2      | PRET INNED vorverzinkt min. 0.8µm                          | 0.5-1.0 FLR          | 1.4-2.3 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927771-9     | M      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.3 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927771-8     | N      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.3 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927771-6     | M      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.3 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 927771-3     | M      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.3 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 3.6<br>K = 3.9<br>D = 1.8 | 3   | 4   | 5.5 | 18.8 | 0.4 |
| 2-927774-1   | C      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.2-0.5 FLR          | 1.0-1.6      | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 2.7<br>K = 2.8<br>D = 1.4 | 2.5 | 3.5 | 5.6 | 18.8 | 0.4 |
| 1-927774-1   | C      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.2-0.5 FLR          | 1.0-1.6      | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 2.7<br>K = 2.8<br>D = 1.4 | 2.5 | 3.5 | 5.6 | 18.8 | 0.4 |
| 927774-6     | B      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.2-0.5 FLR          | 1.0-1.6      | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 2.7<br>K = 2.8<br>D = 1.4 | 2.5 | 3.5 | 5.6 | 18.8 | 0.4 |
| 927774-3     | B      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.2-0.5 FLR          | 1.0-1.6      | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 2.7<br>K = 2.8<br>D = 1.4 | 2.5 | 3.5 | 5.6 | 18.8 | 0.4 |
| 927774-1     | B      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.2-0.5 FLR          | 1.0-1.6      | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 2.7<br>K = 2.8<br>D = 1.4 | 2.5 | 3.5 | 5.6 | 18.8 | 0.4 |
| 963708-1     | B      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.08-0.2 AWG/Special | 1.5-1.8      | E = 1.7<br>G = 1.7<br>D <sub>Dr</sub> = 0.6 | H = 3.1<br>K = 3.2<br>D = 1.6 | 2.5 | 3.7 | 5.9 | 18.8 | 0.4 |
| 969137-1     | A      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 0.2-0.5 FLK          | 1.15-2.3     | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 3.5<br>K = 3.6<br>D = 2.0 | 2.5 | 3.5 | 5   | 18.8 | 0.4 |
| 1-927778-1   | D      | CuFe2      | PRET INNED vorverzinkt min. 0.8µm                          | 0.2-0.5 FLK          | 1.15-2.3     | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 3.5<br>K = 3.6<br>D = 2.0 | 2.5 | 3.5 | 5   | 18.8 | 0.4 |
| 927778-3     | C      | CuSn4      | PRET INNED vorverzinkt min. 0.8µm                          | 0.2-0.5 FLK          | 1.15-2.3     | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 3.5<br>K = 3.6<br>D = 2.0 | 2.5 | 3.5 | 5   | 18.8 | 0.4 |
| 927778-1     | C      | CuFe2      | PRET INNED vorverzinkt min. 0.8µm                          | 0.2-0.5 FLK          | 1.15-2.3     | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 3.5<br>K = 3.6<br>D = 2.0 | 2.5 | 3.5 | 5   | 18.8 | 0.4 |
| 2112132-1    | A      | CuSn4      | PLAIN BLANK  | 0.2-0.5 FLR          | 1.15-1.6     | E = 2.4<br>G = 2.3<br>D <sub>Dr</sub> = 1   | H = 2.9<br>K = 2.9<br>D = 1.4 | 2.5 | 3.5 | 5.6 | 18.8 | 0.2 |
| 2-927766-1   | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLU          | 2.7-3.0 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 18.8 | 0.4 |
| 1-927766-1   | E      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLU          | 2.7-3.0 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 18.8 | 0.4 |
| 927766-3     | D      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLU          | 2.7-3.0 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 18.8 | 0.4 |
| 927766-1     | D      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLU          | 2.7-3.0 FLR  | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 18.8 | 0.4 |
| 2-929937-1   | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 1.5          | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 21   | 0.4 |
| 1-929937-1   | E      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 1.5          | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 21   | 0.4 |
| 929937-6     | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 1.5          | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 21   | 0.4 |
| 929937-3     | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 1.5          | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 21   | 0.4 |
| 929937-1     | E      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 1.5-2.5 FLK          | 1.5          | E = 3.6<br>G = 3.8<br>D <sub>Dr</sub> = 1.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3.5 | 5.9 | 7.5 | 21   | 0.4 |
| 2-929939-1   | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 21   | 0.6 |
| 1-929939-1   | E      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 21   | 0.6 |
| 929939-6     | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 21   | 0.6 |
| 929939-3     | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 21   | 0.6 |
| 929939-1     | E      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 21   | 0.6 |
| 2-927770-1   | G      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 18.8 | 0.6 |
| 1-927770-1   | G      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 18.8 | 0.6 |
| 927770-6     | F      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 18.8 | 0.6 |
| 927770-3     | F      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 18.8 | 0.6 |
| 927770-1     | F      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.5-1.0 FLR          | 1.4-2.1 FLR  | E = 2.6<br>G = 2.8<br>D <sub>Dr</sub> = 1.1 | H = 5.4<br>K = 4.6<br>D = 3.2 | 3   | 5.4 | 7   | 18.8 | 0.6 |
| 2-929941-1   | E      | CuSn4      | PRET INNED vorverzinkt min. 1µm                            | 0.22-0.38 FLK        | 1.16-1.6 FLR | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 5.4<br>K = 4.6<br>D = 3.2 | 2.5 | 4.9 | 6.5 | 21   | 0.9 |
| 1-929941-1   | E      | CuFe2      | PRET INNED vorverzinkt min. 1µm                            | 0.22-0.38 FLK        | 1.16-1.6 FLR | E = 2.1<br>G = 2.1<br>D <sub>Dr</sub> = 0.8 | H = 5.4<br>K = 4              |     |     |     |      |     |