

Features

- Halogen Free. "Green" Device (Note 1)
- AEC-Q101 Qualified
- High Current Capability
- For Surface Mount Application
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Lead Free Finish/RoHS Compliant (Note 2) ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Value							Unit
		SK52A HE3-L	SK53A HE3-L	SK54A HE3-L	SK55A HE3-L	SK56A HE3-L	SK58A HE3-L	SK510A HE3-L	
Peak Repetitive Reverse Voltage	V_{RRM}								V
Working Peak Reverse Voltage	V_{RWM}	20	30	40	50	60	80	100	
DC Blocking Voltage	V_R								
RMS Reverse Voltage	V_{RMS}	14	21	28	35	42	56	70	V
Average Rectified Forward Current	$I_{F(AV)}$	5							A
Non-Repetitive Peak Surge Current @ 8.3ms Half Sine Wave	I_{FSM}	100							A
Current Squared Time @ 1ms ≤ t ≤ 8.3ms	I^2t	41.5							A ² s

Marking Code

Part Number	Marking Code
SK52AHE3-L	SK52A
SK53AHE3-L	SK53A
SK54AHE3-L	SK54A
SK55AHE3-L	SK55A
SK56AHE3-L	SK56A
SK58AHE3-L	SK58A
SK510AHE3-L	SK510A

Internal Structure


Pin	Description	Simplified Outline	Graphic Symbol
1	Cathode	XXXX = Marking Code YYWW = Date Code	
2	Anode		

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

2. High temperature solder exemption applied, see EU directive annex 7a.


5 Amp Surface Mount Schottky Rectifier 20 to 100 Volts

SMA (DO-214AC)



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.075	0.096	1.90	2.44	
B	0.050	0.064	1.27	1.63	
C	0.002	0.008	0.051	0.203	
D	---	0.020	---	0.51	
E	0.030	0.060	0.76	1.52	
F	0.065	0.091	1.65	2.32	
G	0.189	0.220	4.80	5.59	
H	0.157	0.187	4.00	4.75	
J	0.090	0.115	2.25	2.92	

SUGGESTED SOLDER PAD LAYOUT



Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
T _J	Operating Junction Temperature Range		-55		150	°C
T _{stg}	Storage Temperature Range		-55		150	°C
R _{th(J-L)}	Thermal Resistance from Junction to Lead	Note 1		25		°C/W
R _{th(J-A)}	Thermal Resistance from Junction to Ambient	Note 1		80		°C/W

Note:
 1.Mounted on P.C.B. with 8 mm x 8 mm copper pad areas.

Electrical Characteristics @ 25°C Unless Otherwise Specified

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage SK52AHE3-L ~ SK54AHE3-L SK55AHE3-L ~ SK56AHE3-L SK58AHE3-L ~ SK510AHE3-L	V _F	I _F =5A;T _J =25°C			0.55 0.75 0.85	V
Reverse Current	I _R	at Rated V _R ;T _J =25°C at Rated V _R ;T _J =125°C			0.1 20	mA
Junction Capacitance SK52AHE3-L ~ SK54AHE3-L SK55AHE3-L ~ SK56AHE3-L SK58AHE3-L ~ SK510AHE3-L	C _J	V _R =4V;f=1MHz;T _J =25°C		265 215 150		pF

Curve Characteristics

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Forward Characteristics





Fig. 6 - Typical Reverse Leakage Characteristics



Curve Characteristics

Fig. 7 - Typical Forward Characteristics




Fig. 8 - Typical Reverse Leakage Characteristics




Fig. 9 - Capacitance Characteristics




Fig. 10 - Capacitance Characteristics





Fig. 11 - Capacitance Characteristics



Ordering Information

Device	Packing
SK52AHE3-LTP ~ SK510AHE3-LTP	Tape&Reel:5Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.