

SEMiX501D17Fs



SEMiX® 13

SEMiX501D17Fs

Features

- Terminal height 17 mm
- Chips soldered directly to isolated substrate
- UL recognised file no. E63532

Typical Applications*


- Fast Input Bridge Rectifier for AC/DC motor control
- Power supply
- High frequency applications

Absolute Maximum Ratings

Symbol	Conditions		Values	Unit
Rect. Diode				
I _D	T _j = 150 °C	T _c = 85 °C	494	A
	sinus 180°	T _c = 100 °C	417	A
I _{FSM}	10 ms	T _j = 25 °C	2740	A
		T _j = 150 °C	2140	A
i ² t	10 ms	T _j = 25 °C	37538	A ² s
		T _j = 150 °C	22898	A ² s
V _{RSM}			1700	V
V _{RRM}			1700	V
T _j			-40 ... 150	°C
Module				
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50Hz	1 min	4000	V
		1 s	4800	V

Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
Rectifier Diode					
V_F	$T_j = 25\text{ °C}$, $I_F = 300\text{ A}$, chiplevel			1.90	V
$V_{(TO)}$	$T_j = 125\text{ °C}$, chiplevel			1.10	V
r_T	$T_j = 125\text{ °C}$, chiplevel			2.7	mΩ
I_{RD}	$T_j = 125\text{ °C}$, $V_{RD} = V_{RRM}$			14.4	mA
$R_{th(j-c)}$	sin. 180			0.165	K/W
					K/W
Module					
$R_{CC'+EE'}$	measured per switch	$T_c = 25\text{ °C}$	0.7		mΩ
		$T_c = 125\text{ °C}$	1		mΩ
$R_{th(c-s)}$	per chip				K/W
	per module		0.04		K/W
M_s	to heat sink (M5)	3		5	Nm
M_t	to terminals (M6)	2.5		5	Nm
a				5 * 9,81	m/s ²
w				350	g
Temperature Sensor					
R_{100}	$T_c = 100\text{ °C}$ ($R_{25} = 5\text{ kΩ}$)		493 ± 5%		Ω
$B_{100/125}$	$R_{(T)} = R_{100} \exp[B_{100/125}(1/T - 1/T_{100})]$; $T[K]$		3550 ± 2%		K



D




Fig. 4L: Power dissipation per module vs. direct current




Fig. 4R: Power dissipation per module vs. case temperature




Fig. 6: Transient thermal impedance vs. time




Fig. 7: On-state characteristics






Fig. 8: Surge overload current vs. time



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

*IMPORTANT INFORMATION AND WARNINGS

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.