












PC card drilling dimensions(after plating)

(thickness 1.60±0.20mm)



SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	G +0.25 0	PART NUMBER 200 MATING CYCLES	PART NUMBER 500 MATING CYCLES
09	30.81	24.99	16.96	16.21	5.90	D09S23A4G*00LF	D09S23A6G*00LF
15	39.14	33.32	25.18	24.54	5.90	D15S23A4G*00LF	D15S23A6G*00LF
25	53.03	47.04	39.12	38.25	5.70	D25S23A4G*00LF	D25S23A6G*00LF
37	69.32	63.50	55.68	54.71	5.70	D37S23A4G*00LF	D37S23A6G*00LF

Threaded øT M3 = I
Threaded øT 4.40 = V

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

mat'l. code: SEE NOTE				surface: ISO 1302		tolerance: ISO 406 ISO 1101		projection	product family: D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified					title: SOCKET CNRS DELTA D WITH FEMALE SCREW, HARPOON, METAL BRACKET		
C	106-0074	SK	2006-06-08	angles	linear	.0±0.1		mm			
D	ELX-I-281602	DJ	2026-03-12			.00±0.1					
				0°±1°		.000±0.1		scale 1:1			
				dr	JOHN SLEEBA		2000-12-21	Amphenol FCi	dwg no: C01-8646-0755	sheet 1 of 1	size A3
				engr	DIPU JOSEPH		2026-03-12				
				chr	GREGAR M		2026-03-12		type: Product Customer Drawing		
				appd	ALEX BABU		2026-03-12				
sheet index	revision	D									
	sheet	1									

AFCI CONFIDENTIAL
This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AFCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AFCI. © 2016 AFCI

Downloaded from Arrow.com.