





Recommended Panel Cut-Out






Notes:
QC Important Dimension To Check;
Waterproof Rate: IP67;
LED Holder: Brass, Nickel Plating;
LED: Ø3mm, Yellow;
① O-Ring: EPDM, Black;
Screw Nut: Brass, Nickel Plating;
Operating Voltage: DC 4V;
Operating Temperature: -40°C ~ +80°C
For Panel Thickness 6.5mm Max;
Forward Voltage: Yellow Typ. 2.0V/ Max. 2.4(V);
Forward Current: Yellow Max. 30mA;
Reverse Voltage: DC 5V;
Luminous Intensity: Yellow Min. 770/ Max. 1600(Mcd);
Use Unprinted Carton Packaging.







RoHS compliant
Unit: mm

Scale	Free
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
DIM	TOL
Angle	±1°

Id.	Modification	Date	Name
①	Update the notes	06.08.2021	Segal
⓪	Drawn	19.11.2019	Segal

	Date	Name
Drawn	19.11.2019	Segal
Approved	06.08.2021	Segal

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
A-LED8-1YAAS-MR7-1


Drawing-No.
ASS 8506 CO


rev01

Replace

Sheet
1/2

Downloaded from Arrow.com.





RoHS compliant

Unit: mm

Scale	Free
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
DIM	TOL
Angle	±1°

Id.	Modification	Date	Name
①	Update the notes	06.08.2021	Segal
⓪	Drawn	19.11.2019	Segal

	Date	Name
Drawn	19.11.2019	Segal
Approved	06.08.2021	Segal

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
A-LED8-1YAAS-MR7-1

Drawing-No.
ASS 8506 CO

rev01

Replace

Sheet
2/2

Downloaded from Arrow.com.