


PART NO.		MAXIMUM	RADIUS
W/O TAPE	W/TAPE	BUNDLE DIA.	"R"
UMS-16-45	UMS-16-45A-RT	1 (25.4)	1/2 (12.7)
UMS-24-45	UMS-24-45A-RT	1-1/2 (38.1)	3/4 (19.1)
UMS-32-45	UMS-32-45A-RT	2 (50.8)	1 (25.4)







RICHCO RIVET NO.	PANEL THICKNESS RANGE
SR5045	0.000 TO 0.018
SR5055	0.018 TO 0.058
SR5065	0.058 TO 0.097
SR5075	0.097 TO 0.137
SR5085	0.137 TO 0.176
SR5095	0.176 TO 0.215
SR5105	0.215 TO 0.255

NOTES:
1. MATERIAL: NYLON 6/6 (RMS-45).
2. COLOR: BLACK.
3. FOR MOUNTING USE SNAP RIVETS "SR-SERIES", #6 SCREW OR ACRYLIC ADHESIVE TAPE (RMS-15).

REV	DESCRIPTION	ENGR DATE
D	SEE CO 200171 FOR CHANGES	SK 04.29.08
C	SEE ECN #551 FOR CHANGES	SM 01.07.03
B	CHANGED TAPE NOTE AND FILE NO.	SM 12.11.01
A	CHANGED RMS-73 TO RMS-45	JB 04.22.96

TOLERANCES UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

TITLE: UNIVERSAL MOUNTING STRAP

DWG IN IN (MM)

FILE # UMS | DWN: P.B. | APP:

MAT'L: SEE NOTES | DT: 01-18-95 | DT:

RE: RICHCO, INC.

RICHCO INC.
PO BOX 804238,CHICAGO,60680
(773) 539-4060

FINAL

PART # SEE TABLE

PRINT TYPE CA

Downloaded from Arrow.com.