

MLG0603P2N3STD25

**Applications**

Automotive Grade

AEC-Q200

AEC-Q200

**Feature**

Multilayer

Multilayer

Non-Mag Core

Non-Magnetic Core (Dielectric Ceramic)

High Q

High Q

**Series | Type**

MLG-P

**Status**

Production

**Brand**

TDK

**Size**

Length(L)	0.60mm $\pm 0.03$ mm
Width(W)	0.30mm $\pm 0.03$ mm
Thickness   Height	0.30mm $\pm 0.03$ mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

**Electrical Characteristics**

Inductance	2.3nH $\pm 0.3$ nH at 500MHz
Rated Current	600mA
DC Resistance [Typ.]	70m $\Omega$
DC Resistance [Max.]	200m $\Omega$
Self Resonant Frequency [Min.]	7.5GHz
Self Resonant Frequency [Typ.]	8.4GHz
Q [Min.]	14 at 500MHz
Q [Typ.]	18 at 500MHz

**Other**

Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow
AEC-Q200	YES
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.





! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG0603P2N3STD25



## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.



! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG0603P2N3STD25



## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.