Part Number : 787200001
Product Description : 1.27mm Signal Pitch, 0.80mm SCSI Pitch, 1.27mm Power Pitch SAS-3 Receptacle, Vertical, Press-Fit, 2.50mm Peg Length, 2.54mm PCB Thickness, 29 Circuits, Tray, Lead-Free
Series Number : 78720
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

787200001_sd.pdf

787209900-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

EE-78720-901-001.pdf

SP-78720-901-001.zip

Specifications

AS-78720-001-001.pdf

PS-78720-001-001.pdf

TS-78720-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	78720
Description	1.27mm Signal Pitch, 0.80mm SCSI Pitch, 1.27mm Power Pitch SAS-3 Receptacle, Vertical, Press-Fit, 2.50mm Peg Length, 2.54mm PCB Thickness, 29 Circuits, Tray, Lead-Free
Application	Board-to-Board
Component Type	Receptacle
Product Name	SAS 12G,SAS-3
Type	N/A
UPC	887191257778

Agency

CSA	LR19880

Downloaded from Arrow.com.

UL	E29179

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Circuits Detail	Signal 14, Power 15
Circuits (Loaded)	29
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.591/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	2.54mm
PC Tail Length	1.05mm, 1.55mm
Pitch - Mating Interface	0.80mm, 1.27mm
Pitch - Termination Interface	0.80mm, 1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	0° to +55°C

Downloaded from Arrow.com.

Termination Interface Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	SAS / SATA Plugs

This document was generated on Apr 13, 2026

Downloaded from Arrow.com.