

F


E

D

C

B

A



NOTES:

1. RESISTANCE @ 25°C : 100K±1%
2. BETA VALUE (0/50°C) : 3892K±1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +135°C.
4. DISSIPATION FACTOR : 1.5mW/°C
5. THERMAL TIME CONSTANT : LESS THAN 3SECONDS IN WATER
- 6.INSULATION RESISTANCE : 10MΩ AT 100 VDC

RESISTANCE VS TEMPERATURE CHARACTERISTICS:

Temp(°C)	R min (KΩ)	R nom (KΩ)	R max (KΩ)	Temp(°C)	R min (KΩ)	R nom (KΩ)	R max (KΩ)
-40	3081.0	3222.0	3369.0	50	35.160	35.880	36.610
-35	2247.0	2343.0	2442.0	55	29.060	29.710	30.380
-30	1657.0	1722.0	1789.0	60	24.140	24.730	25.330
-25	1233.0	1278.0	1324.0	65	20.150	20.670	21.210
-20	926.6	957.3	989.0	70	16.890	17.360	17.850
-15	700.1	721.3	743.0	75	14.220	14.640	15.080
-10	533.8	548.4	563.4	80	12.020	12.400	12.790
-5	410.4	420.6	430.9	85	10.210	10.550	10.900
0	318.1	325.2	332.3	90	8.705	9.007	9.319
5	248.3	253.2	258.1	95	7.449	7.719	7.999
10	195.3	198.6	202.0	100	6.396	6.638	6.889
15	154.7	157.0	159.3	105	5.511	5.728	5.954
20	123.4	124.9	126.4	110	4.764	4.959	5.162
25	99.000	100.000	101.000	115	4.132	4.307	4.489
30	79.590	80.570	81.550	120	3.594	3.751	3.915
35	64.360	65.290	66.220	125	3.135	3.277	3.425
40	52.340	53.200	54.070	130	2.676	2.803	2.935
45	42.790	43.580	44.380	135	2.217	2.329	2.445

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
	mm		NTS							
	F_A = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				NTC EPOXY - 3892 100MM 100K1%				
F_C = 0	ANGULAR TOL ± °									
F_E = 0	4 PLACES ±									
DIVISIONAL SYMBOLS	3 PLACES ±				EC NO: 657230 DRWN: RAVIKM					