


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	
DESCRIPTION	MATERIAL	FINISH	
GROMMET	100% FLUOROSILICONE	COLOR NATURAL	
SPLICE ASSY HOUSING	EPOXY	COLOR BLACK	
CONTACT FEMALE SOCKET	BERYLLIUM COPPER PER QQ-C-533	PER MIL-T-81714	
CLIP CONTACT RETAINING	BERYLLIUM COPPER PER QQ-C-533 OR STAINLESS STEEL PER QQ-S-766	NONE	
TUBE SHRINK	PER MIL-I-23053/8	COLOR TRANSPARENT	
RESISTOR	SEE PART NO CHART	-	

LDC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	DWN
			B	REV PER ECO-12-005177		15MAR12	PY





RESISTOR 16.5K Ω ,1/20W, \pm 1% (RNC50J1652BS)	591912-6
RESISTOR 100 Ω ,1/20W, \pm 1% (RNC50J1000BS)	591912-5
RESISTOR 10K Ω ,1/10W, \pm 1% (RN55C1002F)	591912-4
RESISTOR 127 Ω ,1/10W, \pm 1% (RNC55H120FS)	591912-3
RESISTOR 100K Ω ,1/10W, \pm 1% (RN55C1003F)	591912-2
RESISTOR 10 Ω ,1/10W, \pm 1% (RN55C10R0F)	591912-1
RESISTOR TYPE	PART NO.

6. MAXIMUM AMBIENT TEMPERATURE AT RATED WATTAGE IS 125°C
- 5

PART NO 591912-3 IS MARKED WITH CUSTOMER PART NO. 127-85-4 WITH .060 MIN HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.
- 4

MARK WIRE SPLICE IDENTIFICATION, "AMP, AMP PART NO AND DATE CODE WITH .060 MIN HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.
3. ENVIRONMENTS CREATED BY THE OPERATION OF INTERNAL ELECTRONIC COMPONENTS WHICH EXCEED THE MODULE RATED PERFORMANCE IS THE RESPONSIBILITY OF THE USER. THE ELECTRONIC COMPONENT SPECIFICATION SHOULD BE CONSULTED.
- 2

MARK WIRE SPLICE WITH RESISTOR SYMBOL  AND WITH Ω (OHM) RATING AT APPROXIMATE AREA SHOWN
1. FOR PIN CONTACT, SEE CUSTOMER USE DRAWING 592404, P/N 2-592404-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	12-22-04	 TE Connectivity			
		CHK	12-22-04				
		D. EABY		NAME			
		APVD	12-22-04				
		D. EABY					
		PRODUCT SPEC					
		APPLICATION SPEC					
		WEIGHT	-				
		CUSTOMER DRAWING					
		SCALE	5: 1				
		SHEET	1 of 1				
		REV	B				