


Performance Data

(Typical values for batteries stored at +25 °C for one year)


System	Lithium Thionyl Chloride
Nominal voltage	3.6 V
Nominal capacity	2.2 Ah
Nominal current	2 mA
Max. continuous discharge current	100 mA
Pulse current capability	200 mA
Anode surface area	14 cm ²
Lithium content	0.65 g
Weight	18 g
Volume	8 cm ³
Temperature range	-55 °C ... +85 °C




SL-760/S




SL-760/T




SL-760/P



SL-760/PR



SL-760/PT




Available Terminations


Termination	Catalogue No.
SL-760/S Standard	11 1 07601 00
SL-760/T Tags	11 1 07602 00
SL-760/P Pins	11 1 07603 00
SL-760/PR Pins radial	11 1 07606 00
SL-760/PT Polarized tags	11 1 07608 00

WARNING:
Fire, explosion, and severe burn hazard. Do not recharge, disassemble, heat above 100 °C, incinerate, or expose contents to water.


Typical Discharge Curves at +25 °C



Available Capacity



Operating Voltage



Voltage Response at +25 °C, Pulse: 20 mA

