

USB 3.0 SuperSpeed to SATA External Hard Drive Docking Station for 2.5in or 3.5in HDD

MODEL NUMBER: U339-000



Description

The USB 3.0 SATA Hard Drive Dock gives you a quick and easy way to set up an external hard drive storage system. Plug the docking station into an available USB 3.0 port on your computer, then insert a 2.5- or 3.5-inch SATA drive for an instant external storage device. Transfer data at SuperSpeed USB 3.0 rates up to 5 Gbps (provided your computer is USB 3.0 capable). Far easier than installing the hard drive internally or in a caddy, the USB 3.0 SATA Dock is easy to use, convenient and practical. Backward compatible to older USB 2.0 and 1.1 computers (480 Mbps and 12 Mbps transfer speeds respectively). Includes 100-240V AC adapter and 4-foot (1.2-meter) USB 3.0 cable. No disk drives are included with this unit. Compatible with Windows (up to 10) and macOS.

Features

- Instant SATA external storage for 2.5" and 3.5" SATA drives
- Plug-n-Play (no software or configuring needed)
- USB 3.0 SuperSpeed transfer rates up to 5 Gbps
- Heavy-weighted base for stability
- Compatible with Windows (up to 10) and Mac

Specifications

OVERVIEW	
UPC Code	037332175588
Technology	SATA/eSATA
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A

Highlights

- Plug in 2.5" or 3.5" SATA drives for instant external storage
- Plug and Play - no tools, software or configuration required
- Connect via USB 3.0 computer port
- Super Speed USB 3.0 - Up to 5 Gbps transfer speeds
- Compatible with Windows (up to 10) and Mac

System Requirements

- 2.5" or 3.5" SATA hard drive
- Computer with an available USB port. USB 3.0 port is required to achieve maximum speeds.
- Compatible with Windows (up to 10) and Mac

Package Includes

- U339-000 USB 3.0 SATA Hard Drive Dock
- USB 3.0 Device Cable
- External Power Supply with NEMA 1-15P Plug (100-240 VAC, 50/60Hz, 0.6A; Output: 12V, 2A)



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

AC Power Adapter Output Specs (V / A)	12V / 2A
AC Power Adapter Cord Length (ft.)	4.9
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A
DC Barrel Plug	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	24
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Power); Blue (Read, Write)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	3.10 x 5.20 x 6.70
Shipping Dimensions (hwd / cm)	7.87 x 13.21 x 17.02
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	2.283 x 5.118 x 2.992
Unit Dimensions (hwd / cm)	5.8 x 13 x 7.6
Unit Packaging Type	Box
Unit Weight (lbs.)	0.55
Unit Weight (kg)	0.25
ENVIRONMENTAL	
Operating Temperature Range	50° to 122°F (10° to 50°C)
Storage Temperature Range	32° to 149°F (0° to 65°C)



Powering Business Worldwide



Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	81.9 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; UL; cUL; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.