




<https://www.wago.com/770-505/021-000>



Color: ■ black



Dimensions in mm

Strain relief housing WINSTA® MIDI 5-pole

The strain relief housing from the WINSTA® MIDI product line is the sophisticated solution for reliable installation. A comprehensive range of accessories complements the WINSTA® product line from WAGO. The WINSTA® MIDI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology facilitates precise electrification. Due to the integrated test slot, it is possible to check connections even when they are plugged in. That saves time and reduces installation labor and costs. A range up to 71 mm can be used for the strip length.

WINSTA® MIDI solutions for your electrical installation – maintenance-free

The WINSTA® Pluggable Connection System is ideally tailored to the very strict requirements of building installation. It makes electrical installation pluggable, and therefore faster, even more reliable, and error-free. Use of this pre-assembled system reduces assembly times and errors during installation at the construction site. Now you can also reduce installation costs without compromising quality and safety: The WINSTA® MIDI accessory reduces the need for servicing and prevents unnecessary downtime.

- for automation controllers
- convenient installation and commissioning

Connection data

Connection 1	
Pole number	5
Connectable sheathed cable diameter	11.5 ... 16.5 mm
Strip length (outer insulation)	71 mm

Physical data

Width	54.75 mm / 2.156 inches
Height	21 mm / 0.827 inches
Depth	72.7 mm / 2.862 inches



Material data		
Note (material data)		<a href="#">Information on material specifications can be found here</a>
Color		black
Material group		I
Insulation material		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.565 MJ
Weight		19.4 g

Environmental requirements		
Processing temperature		-5 ... +40 °C
Continuous operating temperature		-35 ... +85 °C
Note on continuous operating temperature		Insulating parts for temperatures ≤ 105 °C

Commercial data		
eCl@ss 10.0		27-44-06-92
eCl@ss 9.0		27-44-06-92
ETIM 8.0		EC002863
ETIM 7.0		EC002863
PU (SPU)		25 pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454026219
Customs tariff number		39269097900

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

## Approvals / Certificates

### General approvals



Approval	Standard	Certificate Name
cURus Underwriters Laboratories Inc.	UL 1977	E45171
VDE VDE Prüf- und Zertifizierungsinstitut	EN 61535	40029808

## Downloads

### Environmental Product Compliance



Compliance Search			
Environmental Product Compliance 770-505/021-000			

Documentation			
Bid Text			
770-505/021-000	19.02.2019	xml 2.84 KB	
770-505/021-000	10.12.2014	doc 24.00 KB	

CAD/CAE-Data	
<div>CAD data</div> <div>2D/3D Models 770-505/021-000</div> <div></div>	<div>CAE data</div> <div>EPLAN Data Portal 770-505/021-000</div> <div></div> <div>WSCAD Universe 770-505/021-000</div> <div></div> <div>ZUKEN Portal 770-505/021-000</div> <div></div>

1 Compatible Products
1.1 Optional Accessories
1.1.1 Marking
1.1.1.1 Marking strip



[Item No.: 210-333](#)  
Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive; white