




PRODUCT NUMBER	PITCH
OPxx00x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item①Terminal(housing): Thermoplastic (UL94V-0)
- Item②Contact pin: Brass, Tin plated

- Electrical: UL / VDE / TUV
- Voltage rating: 300V / 300V / 300V
 - Current rating: 15A / 12A / 15A
 - Withstanding Voltage: 1.6KV / 2.5KV / 2.5KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval:

N = Number of poles
Dim L=Nx5.0
Dim B=(N-1)x5.0

poles	Tolerance
2-5p	±0.10
6-9p	±0.15
10-13p	±0.20
14-17p	±0.25
18-21p	±0.30
22-24p	±0.40

PART NO.: OP xx 00 x 0 00J0 G

- Solid block
No. of poles
02 2 poles
03 3 poles
...
24 24 poles
- 0 Tin plating 120u" Min RoHS compliant
1 Gold plating 10u" (lead<4%)
2 Gold flash In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK
					angles	MM	title
					dr	scale	TERMINAL BLOCK
					enr		PLUGGABLE SOCKET, VERTICAL, 12.5mm HEIGHT
					chr		dwg no
					appd		sheet 1 of 1 size
							OPxx00x000J0G A4
							type
							CUSTOMER Drawing
sheet index	revision	A					
	sheet	1					