




Micro Commercial Components

Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

Features

- Case Material: Molded Plastic. UL Flammability Classification Rating 94-0 and MSL Rating 1
- Capable of 225Watts of Power Dissipation
- SOT-23 Package For Surface Mount Application
- Low Leakage Current
- Marking : 5BM



Pin Configuration
Top View

Maximum Ratings

- Operating Temperature: -55°C to $+150^{\circ}\text{C}$
- Storage Temperature: -55°C to $+150^{\circ}\text{C}$
- Maximum Thermal Resistance; 556°C/W Junction To Ambient

Electrical Characteristics @ 25°C Unless Otherwise Specified

Reverse Voltage	V_R	70V	
Minimum Reverse Breakdown Voltage	V_{BR}	70V	$I_{BR}=100\mu\text{A}$
Forward Current	I_F	200mA	
Power Dissipation FR-5 Board ⁽¹⁾	P_{TOT}	225mW $1.8\text{mW}/^{\circ}\text{C}$	$T_A=25^{\circ}\text{C}$ Derate above 25°C
Power Dissipation Alumina Substrate ⁽²⁾	P_{TOT}	300mW $2.4\text{mW}/^{\circ}\text{C}$	$T_A=25^{\circ}\text{C}$ Derate above 25°C
Peak Forward Surge Current	I_{FSM}	500mA	8.3ms, half sine
Junction Temperature	T_J	150°C	
Forward Voltage	V_F	0.55~0.7V 0.85~1.1V	$I_F=1.0\text{mA}$ $I_F=100\text{mA}$
Maximum Reverse Voltage Leakage Current	I_R	0.1 μA	$V_R=50\text{V}$ $T_A=25^{\circ}\text{C}$,
Maximum Junction Capacitance	C_J	2.5pF	Measured at $V_R=0\text{V}$
Maximum Reverse Recovery Time	T_{rr}	4.0nS	$I_F=I_R=10\text{mA}$ $I_R(RCE)=1.0\text{mA}$




1) FR-5= $1.0 \times 0.75 \times 0.062$ in.

2) Alumina= $0.4 \times 0.3 \times 0.024$ in. 99.5% alumina.

MMBD6100


Monolithic Dual Switching Diode

SOT-23



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.110	.120	2.80	3.04	
B	.083	.098	2.10	2.64	
C	.047	.055	1.20	1.40	
D	.035	.041	.89	1.03	
E	.070	.081	1.78	2.05	
F	.018	.024	.45	.60	
G	.0005	.0039	.013	.100	
H	.035	.044	.89	1.12	
J	.003	.007	.085	.180	
K	.015	.020	.37	.51	

Suggested Solder Pad Layout



MMBD6100

MCC

Micro Commercial Components




Figure 1. Recovery Time Equivalent Test Circuit




Figure 2. Forward Voltage




Figure 3. Leakage Current




Figure 4. Capacitance

www.mccsemi.com



Micro Commercial Components

Ordering Information

Device	Packing
(Part Number)-TP	Tape&Reel;3Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . *Micro Commercial Components Corp.* does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp.* and all the companies whose products are represented on our website, harmless against all damages.

APPLICATIONS DISCLAIMER

Products offer by *Micro Commercial Components Corp.* are not intended for use in Medical, Aerospace or Military Applications.

www.mccsemi.com