

Specifications



Photo is representative



Eaton EFPLA1DJ224C102LH

Eaton FILM CAP EFPLA, 1300VDC, 0.22uF, J, 2LEADS, Size=26mmx29.5mmx14.5mm

General specifications

PRODUCT NAME	Eaton EFPLA metallized polypropylene film pulse capacitors
CATALOG NUMBER	EFPLA1DJ224C102LH
UPC	197162038559
PRODUCT LENGTH/DEPTH	26 mm
PRODUCT HEIGHT	14.5 mm
PRODUCT WIDTH	29.5 mm
PRODUCT WEIGHT	13.6 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Metallized polypropylene film pulse capacitors

Product specifications

VOLTAGE RATING	1300 Vdc
IRMS	8.5 A
PEAK CURRENT	330 A
EQUIVALENT SERIES RESISTANCE (ESR)	9.5 mΩ @ 10 kHz
EQUIVALENT SERIES INDUCTANCE (ESL)	15 nH
DV/DT	1500 V/μs
TEMPERATURE RATING	-55 °C to +105 °C
SIZE	26 mm x 14.5 mm x 29.5 mm
GRADE	Automotive THB Grade IIIB

Resources

APPLICATION NOTES

[Understanding Eaton's film capacitors \(Safety, DC-Link, Pulse and AC-filtering\)](#)

BROCHURES

[Eaton capacitors provide reliable EMI filtering in distributed solar inverters](#)

[Eaton's film capacitors provide reliable EMI filtering in fast-charging xEV stations](#)

[Eaton's film capacitors provide reliable EMI filtering in onboard chargers for electric vehicles](#)

[Eaton offers standard and automotive-grade film capacitors for electronic applications](#)

SPECIFICATIONS AND DATASHEETS

[EFPLA Pulse film capacitor data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

