



■ **Features**

- Input voltage: 90-305VAC
- Built-in active PFC function: 0.99 Typ.
- Low THD: 10% Typ.
- High efficiency: 93.5% Typ.
- IP67 design for indoor or outdoor installations
- High surge immunity
- Compliance to worldwide safety regulations for lighting
- Suitable for dry/damp locations





■ **Specification**


Model																			
(MU200HxxxAQ) (1)		035	045	053	070	085	105	120	140	150	175	210	245	280	300	315	350	420	490
(MU200HxxxAQ_II) (2)		560	600																
Input	Efficiency(120Vac)(Typ.) _{Note.1}	90.0%	90.0%	90.0%	90.0%	90.0%	89.0%	89.0%	89.0%	89.0%	89.0%	89.0%	89.0%	89.0%	88.0%	88.0%	88.0%	88.0%	88.0%
	Efficiency(230Vac)(Typ.) _{Note.1}	93.0%	93.0%	93.0%	93.0%	93.0%	92.0%	92.0%	92.0%	92.0%	92.0%	92.0%	92.0%	92.0%	91.0%	91.0%	91.0%	91.0%	91.0%
	Voltage Range (V) _{Note.2}	90~305Vac, OR 127~ 430Vdc (Derating may be need under low inputs, Refer to 'Derating Curve')																	
	Voltage Rate (V) _{Note.2}	100Vac-277Vac																	
	Frequency Range (Hz)	47~63																	
	Power Factor(Typ.)	0.99 (Typ.) with 80%~100% load,at 120Vac																	
		0.96 (Typ.) with 80%~100% load,at 230Vac																	
		>0.9 with 80%~100% load,at 277Vac																	
	THD(Typ.)	<10% at 220VAC input 50Hz,80%~100% load																	
		<15% at 110VAC and 277VAC input 60Hz,80%~100% load																	
Output	AC Current(Typ.)	2.4A at 100VAC input, 1.2A at 230VAC																	
	Inrush Current(Max.)	65A at 230Vac input 25°C Cold Start (time wide=500uS, measured at 50% Ipeak,Not applicable for the inrush current to Noise Filter for less than 0.2ms)																	
	Leakage Current(Max.)	0.75mA at 277VAC/60Hz input for class I;0.5mA at 277VAC/60Hz input for classII																	
	Voltage range (V)	286-571	222-444	189-377	143-285	118-235	95-190	83-166	71-142	67-133	57-114	48-95	41-81	36-71	34-67	32-63	29-57	24-48	20-40
	Rated Current(mA)	350	450	530	700	850	1050	1200	1400	1500	1750	2100	2450	2800	3000	3150	3500	4200	4900
	Rated Power (W)	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200
	Ripple&Noise Current(Typ.)	≤10%((PK-AV) /AV) with LED default mode and full load)																	
	Current Tolerance	±5%																	
	Line Regulation	±1%																	
	Load Regulation	±3%																	
Protection	Over Voltage(V)	799	622	528	399	329	266	232	199	186	160	133	113	99	94	88	80	67	56
	Short Circuit	Hiccup mode.The power supply shall be self-recovery when the fault is removed.																	
	Over temperature	Protection type : Decrease output current . When TC reaches 105±10°C , the output current decrease to 50% rate value until the TC reaches 75±15°C																	
Environment	Operating Temp.	-40~+70°C(Refer to 'Derating Curve')																	
	Tc	90°C max																	
	Operating Humidity	20~95%RH																	
	Storage Temp., Humidity	-40~+80°C , 10-95%RH																	
	Temp. Coefficient	0.03%/°C (0~50°C)																	
Safety & EMC	Vibration	10-500Hz,5G 12min/cycle , period for 72min each along X、 Y、 Z axes																	
	Safety Standard	UL8750, UL1012, CAN/CSA-C22.2No.107.1-01,EN61347-1, EN61347-2-13 ,EN60598-1,EN62384,GB19510.1,GB19510.14,GB7000.1																	
	Withstand Voltage	I/P-O/P:3.75KVAC I/P-FG:1.875KV O/P-FG:1.5KV for class I;I/P-O/P:3.75KVAC I/P-Case:3.75KV O/P--Case:1.5KV for class II																	
	Isolation Resistance	I/P-O/P ,I/P-FG,O/P-FG:100M Ohms/500VDC/25°C/70%RH for class I;I/P-O/P ,I/P-Case,O/P-Case:100M Ohms/500VDC/25°C/70%RH for class II																	
	EMC Emission	EN55015/FCC Part 15 Class B , EN61000-3-2 Class C , EN61000-3-3																	
Others	EMC Immunity	EN61000-4-2,3,4,5,6,8,11 (Surge L,N-FG 6KV , L-N 4KV) , EN61547 for class I;EN61000-4-2,3,4,5,6,8,11 (Surge L,N-Case 4KV , L-N 4KV) , EN61547 for class II																	
	MTBF	300,000 Hours,measured at full load,25°C ambient temperature																	
	Lifetime	50,000 Hours at Tc 75°C(Refer to"Life Time VS. Tcase (Ref.)")																	
	Dimension	251 x 67.5 x 40 (mm) (LxWxH)																	
Weight		1.2kg(Typ.)																	

Note.1: Measured at full load and steady-state temperature in 25°C ambient(Efficiency will be about 2% lower if measured immediately after startup); Note. 2: Derating may be needed under low input voltages , Please Refer to 'Derating Curve' ; Note. 3: All parameters NOT specially mentioned are measured at 230VAC input , rated load and 25°C of ambient temperature ;


Derating Curve




Power Factor VS. Load Curve




Efficiency VS. Load Curve



THD Curve




Life Time VS. Tcase (Ref.)



■ Mechanical Specification

1. Dimensions (Unit: mm)



RoHS Compliance:

Our products comply with the European Directive 2002/95/EC, calling for the elimination of lead and other hazardous substances from electronic products.

2. Terminal wire Type

Products	AC Input			DC output		
	Wire Type	Assignment	Description	Wire Type	Assignment	Description
ENEC/CE approval for class II	RUBBER CCC+VDE 60245 IEC57 YZW/H05RN-F	BROWN/L	2*1.0mm ² ODΦ 6.8± 0.3mm	RUBBER CCC+VDE 60245 IEC57 YZW/H05RN-F	Brown/+	2*1.0mm ² ODΦ 6.8± 0.3mm
		BLUE/N			Blue/-	
UL approval	UL SJTW PVC	BLACK/L	3*AWG#18	UL SJTW PVC	RED/+	2*AWG#18
		WHITE/N			BLUE/-	
		GREEN/GN				
PSE approval	PSE HVCTF/VCTF/VCTFK PVC	BLACK/L	3*0.75mm ² ODΦ 6.8± 0.3mm	PSE HVCTF/VCTF/VCTFK PVC	WHITE/+	2*0.75mm ² ODΦ 6.7± 0.3mm
		WHITE/N			BLACK/-	
		YE-GN/GND				
CCC/CB/CE approval	RUBBER CCC+VDE 60245 IEC57 YZW/H05RN-F	BROWN/L	3*1.0mm ² ODΦ 7.3± 0.3mm	RUBBER CCC+VDE 60245 IEC57 YZW/H05RN-F	Brown/+	2*1.0mm ² ODΦ 6.8± 0.3mm
		BLUE/N			Blue/-	
		YE-GN/GND				

subject to change without notice

Page 3 of 3

SHANGHAI MOONS' AUTOMATION CONTROL CO., LTD.

Add: No.168, Mingjia Road, Shanghai 201107, P.R.China

Tel: +86 (0)21 52634688 Website: www.moons.com.cn