



DATE	REV	ECN	APP'D. BY
5/27/22	A0	11991	JE









RECOMMENDED PCB FOOTPRINT (COMPONENT SIDE)

NOTES:

1. CONNECTOR MATERIALS
   HOUSING: THERMOPLASTIC UL94 V-0
   CONTACT PLATING: SELECTIVE GOLD OR EQUIVALENT
   IN THE CONTACT AREA
   SEE CHART FOR PART NUMBER
2. OPERATING LIFE: 750 CYCLES MIN
3. DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.
4. ELECTRICAL
   VOLTAGE RATING: 150 VAC RMS
   CURRENT RATING: 1.5 AMP
   CONTACT RESISTANCE: 20 mΩ MAX
   INSULATION RESITANCE: 1000 MΩ MIN @ 500 VDC.
   DIELECTRIC STRENGTH: 1000V DC OR AC PEAK; CONTACT TO CONTACT
   1500V DC OR AC PEAK; CONTACTS TO SHIELD
5. ENVIRONMENTAL
   STORAGE TEMPERATURE: -40° C TO 85° C
   OPERATIONAL TEMPERATURE: -40° C TO 85° C

15 MICRO-INCHES [0.76um]	SS-90000-011
CONTACT PLATING IN MATING AREA	PART NUMBER

RoHS

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°

SHEET NO. 1 OF 1

stewart CONNECTOR a bel group

11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512
http://www.stewartconnector.com

TITLE: RJ45 SHIELDED ESSENTIALS JACK

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/

DRN BY:	BTS	DATE	03/07/22
APPD BY:	JE	DATE	05/27/22
DWG NO.	CT900011	REV.	A0

AutoCAD

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.