


EPC2102 – Enhancement-Mode GaN Power Transistor Half-Bridge


 $V_{DS}, 60\text{ V}$
 $R_{DS(on)}, 4.9\text{ m}\Omega$
 $I_D, 30\text{ A}$


Gallium Nitride's exceptionally high electron mobility and low temperature coefficient allows very low $R_{DS(on)}$, while its lateral device structure and majority carrier diode provide exceptionally low Q_G and zero Q_{RR} . The end result is a device that can handle tasks where very high switching frequency, and low on-time are beneficial as well as those where on-state losses dominate.

Maximum Ratings				
DEVICE	PARAMETER		VALUE	UNIT
Q1 & Q2	V_{DS}	Drain-to-Source Voltage (Continuous)	60	V
		Drain-to-Source Voltage (up to 10,000 5 ms pulses at 150°C)	72	
	I_D	Continuous ($T_A = 25^\circ\text{C}$, $R_{\theta JA} = 15^\circ\text{C/W}$)	30	A
		Pulsed (25°C , $T_{PULSE} = 300\text{ }\mu\text{s}$)	220	
	V_{GS}	Gate-to-Source Voltage	6	V
		Gate-to-Source Voltage	-4	
	T_J	Operating Temperature	-40 to 150	$^\circ\text{C}$
	T_{STG}	Storage Temperature	-40 to 150	

Thermal Characteristics				
	PARAMETER		TYP	UNIT
Q1 & Q2	$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	0.3	$^\circ\text{C/W}$
	$R_{\theta JB}$	Thermal Resistance, Junction-to-Board	2.2	
	$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient (Note 1)	42	

Note 1: $R_{\theta JA}$ is determined with the device mounted on one square inch of copper pad, single layer 2 oz copper on FR4 board. See https://epc-co.com/epc/documents/product-training/Appnote_Thermal_Performance_of_eGaN_FETs.pdf for details



EPC2102 eGaN® ICs are supplied only in passivated die form with solder bumps
Die Size: 6.05 mm x 2.3 mm

Applications

- High Frequency DC-DC

Benefits

- High Frequency Operation
- Ultra High Efficiency
- High Density Footprint

Static Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise stated)							
DEVICE	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
Q1 & Q2	BV_{DSS}	Drain-to-Source Voltage	$V_{GS} = 0\text{ V}$, $I_D = 0.6\text{ mA}$	60			V
	I_{DSS}	Drain-Source Leakage	$V_{DS} = 48\text{ V}$, $V_{GS} = 0\text{ V}$		0.008	0.4	mA
	I_{GSS}	Gate-to-Source Forward Leakage	$V_{GS} = 5\text{ V}$		0.015	7	mA
		Gate-to-Source Reverse Leakage	$V_{GS} = -4\text{ V}$		0.008	0.4	mA
	$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 7\text{ mA}$	0.8	1.3	2.5	V
	$R_{DS(on)}$	Drain-Source On Resistance	$V_{GS} = 5\text{ V}$, $I_D = 20\text{ A}$		3.6	4.9	m Ω
	V_{SD}	Source-Drain Forward Voltage	$I_S = 0.5\text{ A}$, $V_{GS} = 0\text{ V}$		1.7		V

Dynamic Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise stated)

DEVICE	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
Q1	C_{ISS}	Input Capacitance	$V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}$		850	1020	pF
	C_{RSS}	Reverse Transfer Capacitance			11		
	C_{OSS}	Output Capacitance			500	750	
	$C_{OSS(ER)}$	Effective Output Capacitance, Energy Related (Note 2)	$V_{DS} = 0\text{ to }30\text{ V}, V_{GS} = 0\text{ V}$		695		
	$C_{OSS(TR)}$	Effective Output Capacitance, Time Related (Note 3)			863		
	Q_G	Total Gate Charge	$V_{DS} = 30\text{ V}, V_{GS} = 5\text{ V}, I_D = 20\text{ A}$		8	11	nC
	Q_{GS}	Gate-to-Source Charge	$V_{DS} = 30\text{ V}, I_D = 20\text{ A}$		2.5		
	Q_{GD}	Gate-to-Drain Charge			1.5		
	$Q_{G(TH)}$	Gate Charge at Threshold			1.7		
	Q_{OSS}	Output Charge	$V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}$		26	39	
	Q_{RR}	Source-Drain Recovery Charge			0		
Q2	C_{ISS}	Input Capacitance	$V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}$		850	1020	pF
	C_{RSS}	Reverse Transfer Capacitance			11		
	C_{OSS}	Output Capacitance			610	915	
	$C_{OSS(ER)}$	Effective Output Capacitance, Energy Related (Note 2)	$V_{DS} = 0\text{ to }30\text{ V}, V_{GS} = 0\text{ V}$		830		
	$C_{OSS(TR)}$	Effective Output Capacitance, Time Related (Note 3)			1030		
	Q_G	Total Gate Charge	$V_{DS} = 30\text{ V}, V_{GS} = 5\text{ V}, I_D = 20\text{ A}$		8	11	nC
	Q_{GS}	Gate-to-Source Charge	$V_{DS} = 30\text{ V}, I_D = 20\text{ A}$		2.5		
	Q_{GD}	Gate-to-Drain Charge			1.5		
	$Q_{G(TH)}$	Gate Charge at Threshold			1.7		
	Q_{OSS}	Output Charge	$V_{DS} = 30\text{ V}, V_{GS} = 0\text{ V}$		31	47	
	Q_{RR}	Source-Drain Recovery Charge			0		

Note 2: $C_{OSS(ER)}$ is a fixed capacitance that gives the same stored energy as C_{OSS} while V_{DS} is rising from 0 to 50% BV_{DSS} .

Note 3: $C_{OSS(TR)}$ is a fixed capacitance that gives the same charging time as C_{OSS} while V_{DS} is rising from 0 to 50% BV_{DSS} .


Figure 1 (Q1 & Q2): Typical Output Characteristics at 25°C 

Figure 2 (Q1 & Q2): Transfer Characteristics






Figure 3 (Q1 & Q2): $R_{DS(on)}$ vs. V_{GS} for Various Drain CurrentsFigure 4 (Q1 & Q2): $R_{DS(on)}$ vs. V_{GS} for Various Temperatures

Figure 5a (Q1): Capacitance (Linear Scale)




Figure 5b (Q1): Capacitance (Log Scale)




Figure 5c (Q2): Capacitance (Linear Scale)




Figure 5d (Q2): Capacitance (Log Scale)






Figure 6a (Q1): Output Charge and C_{oss} Stored EnergyFigure 6b (Q2): Output Charge and C_{oss} Stored Energy

Figure 7 (Q1 & Q2): Gate Charge




Figure 8 (Q1 & Q2): Reverse Drain-Source Characteristics




Figure 9 (Q1 & Q2):
Normalized On-State Resistance vs. TemperatureFigure 10 (Q1 & Q2):
Normalized Threshold Voltage vs. Temperature

Figure 11a
Transient Thermal
Response Curves




Figure 11b
Transient Thermal
Response Curves




Figure 12 (Q1 & Q2): Safe Operating Area






Figure 13: Typical Application Circuit



TAPE AND REEL CONFIGURATION

8 mm pitch, 12 mm wide tape on 7" reel




EPC2102 (Note 1)	Dimension (mm)		
	Target	MIN	MAX
a	12.00	11.90	12.30
b	1.75	1.65	1.85
c (Note 2)	5.50	5.45	5.55
d	4.00	3.90	4.10
e	8.00	7.90	8.10
f (Note 2)	2.00	1.95	2.05
g	1.50	1.50	1.60
h	1.50	1.50	1.75

Note 1: MSL 1 (moisture sensitivity level 1) classified according to IPC/JEDEC industry standard.

Note 2: Pocket position is relative to the sprocket hole measured as true position of the pocket, not the pocket hole.


DIE MARKINGS



Part Number	Laser Markings		
	Part # Marking Line 1	Lot Date Code Marking Line 2	Lot Date Code Marking Line 3
EPC2102	2102	YYYY	ZZZZ

DIE OUTLINE

Solder Bump View



DIM	MIN	Nominal	MAX
A	6020	6050	6080
B	2270	2300	2330
c	400	400	400
d	450	450	450
e	210	225	240
f	187	208	229


Pad 2 is G1; Pad 3 is Q1 Gate Return; Pad 4 is G2;

Pads 1, 11, 12, 13, 21, 22, 23, 31, 32, 33, 41, 42, 51, 52, 61, 62, 71, 72 are V_{IN} ;

Pads 5, 14, 15, 24, 25, 34, 35, 43, 44, 45, 53, 54, 55, 63, 64, 65, 73, 74, 75 Ground;


Pads 6, 7, 8, 9, 10, 16, 17, 18, 19, 20, 26, 27, 28, 29, 30, 36, 37, 38, 39, 40, 46, 47, 48, 49, 50, 56, 57, 58, 59, 60, 66, 67, 68, 69, 70 are Switch Node

RECOMMENDED LAND PATTERN

(measurements in μm)

The land pattern is solder mask defined.
Suggest SMD Pads at $200 +20/-10 \mu\text{m}$.
 $190 \mu\text{m}$ minimum.

RECOMMENDED STENCIL DRAWING

(measurements in μm)

Recommended stencil should be 4 mil ($100 \mu\text{m}$) thick, must be laser cut, openings per drawing.

Intended for use with SAC305 Type 4 solder, reference 88.5% metals content.

Additional assembly resources available at:
<https://epc-co.com/epc/DesignSupport/AssemblyBasics.aspx>

Efficient Power Conversion Corporation (EPC) reserves the right to make changes without further notice to any products herein to improve reliability, function or design. EPC does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

eGaN® is a registered trademark of Efficient Power Conversion Corporation.
EPC Patent Listing: epc-co.com/epc/AboutEPC/Patents.aspx

Information subject to change without notice.

Revised June, 2020