


DRAWING MADE IN THIRD ANGLE PROJECTION
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.


| LOC | DIST |
|---|---|
| AR | 39 |

| P | F | ZONE | LTR | REVISIONS DESCRIPTION | DATE | APPD |
|---|---|---|---|---|---|---|
| | | | J | REV&REDRAWN ECN 2275 | — | — |
| | | | K | REACTIVATE 3-1 PER ECN BD3808 | 4-3-90 | GDM |
| | | | L | REV PER ECN BD4149 | 8-15-90 | — |
| | | | M | REV PER EC BD6679 | 03/04/93 | GDM |
| | | | N | OBSOLETE -38 PER EC 0020-0943-93 | 11/18/93 | DK |
| | | | P | SUPSD -4,-6,-8,-16,-18,-24, -26,-28,-30,-32,-34,-36 PER EC 0020-0700-94 | 04/24/95 | DK |
| | | | R | OBS -2,-10,-14 PER EC 0020-0680-94 | 04/24/95 | DK |
| | | | 01 | REVISED PER ECO-09-020774 | 21AUG09 | AEG |









CRIMPED CONTACTS INSERTED FOR REFERENCE ONLY




1. HOUSING WILL ACCOMMODATE FLEXIBLE FLAT CABLE .050 OR .062 WIDE CONDUCTORS ON .100 CENTERS AND/OR #22-32 AWG WIRE WITH INSULATION RANGE OF .025 TO .056
2. AMP TRADEMARK MOLDED IN THIS AREA
3. PART NO. AND DATE CODE INK STAMPED, WHITE.
4. CONTACT POSITION NOS. INK STAMPED, WHITE, BOTH SIDES (SEE TABLE)
5. INDICATES POSITION 1
6. PART NO. SUPERSEDED BY AS MOLDED PART NO.
7. OBSOLETE PART NO.

8

| PART NUMBER | SUPERSEDED BY |
|---|---|
| 86673-4 | 88179-6 |
| 86673-6 | 88179-5 |
| 86673-8 | 2-88179-2 |
| 1-86673-6 | 2-88179-4 |
| 1-86673-8 | 1-88179-4 |
| 2-86673-4 | 3-88179-0 |
| 2-86673-6 | 2-88179-0 |
| 2-86673-8 | 1-88179-2 |
| 3-86673-0 | 3-88179-2 |
| 3-86673-2 | 88179-4 |
| 3-86673-4 | 3-88179-4 |
| 3-66673-6 | 3-88179-6 |

9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

| | NEAR SIDE | FAR SIDE | | | | | |
|---|---|---|---|---|---|---|---|
| INK STAMPED PART NO. | CAVITY POSN NO. STAMPED | | C | B | A | NO OF POSN | AS MOLDED PART NO. |
| 6 3-86673-7 | 2,5,10 | 12,15,22 | 1.350 | 1.234 | 1.280 | 22 | 7 3-86673-8 |
| 6 3-86673-5 | 2,5,10,16 | 18,25,30,34 | 1.950 | 1.834 | 1.880 | 34 | 8 3-86673-6 |
| 6 3-86673-3 | 2,5 | 7,12 | .850 | .734 | .780 | 12 | 8 3-86673-4 |
| 3-86673-1 | 2,5,10,15,20,25,29 | 31,35,40,45,50,55,60 | 3.250 | 3.134 | 3.180 | 60 | 8 3-86673-2 |
| 6 2-86673-9 | 2 | 4,6 | .550 | .434 | .480 | 6 | 8 3-86673-0 |
| 6 2-86673-7 | 2,5,10,15,20,24 | 26,30,35,40,45,50 | 2.750 | 2.634 | 2.680 | 50 | 8 2-86673-8 |
| 6 2-86673-5 | 2,5,10,17 | 19,25,30,36 | 2.050 | 1.934 | 1.980 | 36 | 8 2-86673-6 |
| 6 2-86673-3 | 2,4 | 6,10 | .750 | .634 | .680 | 10 | 8 2-86673-4 |
| 6 2-86673-1 | 2,5,10,13 | 15,20,25,28 | 1.650 | 1.534 | 1.580 | 28 | 2-86673-2 |
| 6 1-86673-9 | 2,5,12 | 14,20,26 | 1.550 | 1.434 | 1.480 | 26 | 2-86673-0 |
| 6 1-86673-7 | 2,5,11 | 13,20,24 | 1.450 | 1.334 | 1.380 | 24 | 8 1-86673-8 |
| 6 1-86673-5 | 2,5,10,15,21 | 23,30,35,40,44 | 2.450 | 2.334 | 2.380 | 44 | 8 1-86673-6 |
| 6 1-86673-3 | 2,5,10,15,20,25,28 | 30,35,40,45,50,55,58 | 3.150 | 3.034 | 3.080 | 58 | 7 1-86673-4 |
| 6 1-86673-1 | 2,5,8 | 10,15,18 | 1.150 | 1.034 | 1.080 | 18 | 9 ~~1-86673-2~~ |
| 6 86673-9 | 2,5,10,15,20,25,32 | 34,40,45,50,55,60,66 | 3.550 | 3.434 | 3.480 | 66 | 7 1-86673-0 |
| 6 86673-7 | 2,5,10,15,19 | 21,25,30,35,40 | 2.250 | 2.134 | 2.180 | 40 | 8 86673-8 |
| 6 86673-5 | 2,5,9 | 11,15,20 | 1.250 | 1.134 | 1.180 | 20 | 8 86673-6 |
| 6 86673-3 | 2,5,10,15,18 | 20,25,30,35,38 | 2.150 | 2.034 | 2.080 | 38 | 8 86673-4 |
| 6 86673-1 | 2,5,10,15,20,25,30,34 | 36,40,45,50,55,60,65,70 | 3.750 | 3.634 | 3.680 | 70 | 7 86673-2 |

PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON :
2 PLC DEC ± -
3 PLC DEC ± .005
ANGLES ± -

MATERIAL
NYLON, GLASS FILLED
COLOR: BLACK

FINISH
-

DR 2/16/89 J. GALLUCCI
CHK 3-3-89 D.ROCKER
APPD 3-3-89 G.D.MILLER
APPD 3-3-89 W.PARKER
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

AMP | AMP INCORPORATED Harrisburg, Pa. 17105

NAME
HOUSING, RCPT, DBL ROW,
.100 , FFC

SIZE D | FSCM NO 00779 | DRAWING NO 86673
SCALE 4:1 | SHEET 1 OF 1

CUSTOMER DRAWING


Transcribed 061116.074051 (YYMMDD.HHMMSS) from Computervision, Inc., Medusa Revision 12.2.57

Downloaded from Arrow.com.