

Part Number : 1202540112
Product Description : Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, PNP, Light-ON/IOL, 2m 3-wire PVC Cable, 33mm Housing Length
Series Number : 120254
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : LTR-M18PA-NMK-403

Obsolete

Documents and Resources

Specifications

1202540112-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Photoelectric Sensors
Series	120254
Description	Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, PNP, Light-ON/IOL, 2m 3-wire PVC Cable, 33mm Housing Length
IP Rating	IP67
Operating Principle	Diffuse
Product Name	Contrinex
Type	Photoelectric
UPC	191130068388

Electrical

Output	Light-ON/IOL
Polarity	PNP

Physical

Connection	Cable (PVC 2m, 3-wire)
Length	33mm
Material - Housing	ABS
Material - Window	PMMA
Operating Distance	3 - 1200mm
Output	Light-ON/IOL
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C

Obsolete

Downloaded from Arrow.com.