



HONEYWELL PART NUMBER
11SM303-T2
PRODUCT CODE TWW9990

REV	DOCUMENT	CHANGED BY	CHECK
9	0038104	PK 23APR08	ASD




PLASTIC PLUNGER



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
 - 4 - MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	PR-2645
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ±			DRAWN	VK	27 NOV 07		Honeywell				
OPERATING FORCE — — — — 3 - 5 OZ		CONTACT ARRANGEMENT SPDT						CHECK	RJ	27 NOV 07						
RELEASE FORCE — — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC					
DIFFERENTIAL TRAVEL — — — .004 MAX			SEA LEVEL	50,000 FT												
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE	1/2 AMP	1/2 AMP	THIRD ANGLE PROJECTION 			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV	
		RESISTIVE	1 AMP	1 AMP							B	I	11SM303-T2		9	
		APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4		05	CE									
			UL, CSA	1A, 125 VAC		CS	BRAND									
							L 22									
								RASTER			SCALE	-	WEIGHT .006 LB		SHEET	1 OF 1