







Printed board layout
component side



A

09 66 215 3501	M3	1					Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-sub, High temperature, 15 poles, female, straight, with solder pins 2.9, and nuts.	Maßstab/ Scale 1,5:1
09 66 215 6501	M3	2					Detail.	05/03/02	CV		
09 66 215 7501	M3	3					Insp.				
09 66 215 3502	4-40 UNC	1					Stand.				
09 66 215 6502	4-40 UNC	2	31892	05/05/04	JH	HARTING EURL F-95972 Paris				TB 09 66 215 x50x	Blatt/ Page 2
09 66 215 7502	4-40 UNC	3	29723	05/03/02	CV						
Part number	Nut thread	Performance level	Mod.	Dat.	Name						