

2N2322 2N2326
 2N2323 2N2327
 2N2324 2N2328
 2N2325 2N2329

SILICON CONTROLLED RECTIFIER
1.6 AMPS, 25 THRU 400 VOLTS



TO-39 CASE

CentralTM

Semiconductor Corp.

DESCRIPTION:

The CENTRAL SEMICONDUCTOR 2N2322 Series types are hermetically sealed Silicon Controlled Rectifiers designed for sensing circuit applications and control systems.

MARKING: FULL PART NUMBER

MAXIMUM RATINGS: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

MAXIMUM RATINGS: (T _C =25°C unless otherwise noted)					2N23__					
	SYMBOL	<u>22</u>	<u>23</u>	<u>24</u>	<u>25</u>	<u>26</u>	<u>27</u>	<u>28</u>	<u>29</u>	UNITS
Peak Repetitive Forward Voltage	V _{DRM}	25	50	100	150	200	250	300	400	V
Peak Repetitive Reverse Voltage	V _{RRM}	25	50	100	150	200	250	300	400	V
Non-Repetitive Peak Reverse Voltage	V _{RSM}	40	75	150	225	300	350	400	500	V
RMS On-State Current	I _T (RMS)					1.6				A
Average On-State Current (T _C =85°C)	I _T (AV)					1.0				A
Peak One Cycle Surge (t=8.3ms)	I _{TSM}					15				A
Peak Gate Power	P _{GM}					0.10				W
Average Gate Power	P _G (AV)					0.01				W
Peak Gate Current	I _{GM}					0.10				A
Peak Gate Voltage	V _{GM}					6.0				V
Junction Temperature	T _J				-65 to +125					°C
Storage Temperature	T _{stg}				-65 to +150					°C


ELECTRICAL CHARACTERISTICS: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
I_{DRM}, I_{RRM}	Rated $V_{DRM}, V_{RRM}, R_{GK}=1.0\text{k}\Omega$		5.0	μA
I_{GT}	$V_D=6.0\text{V}, R_L=100\Omega$		200	μA
I_H	$V_D=6.0\text{V}, R_{GK}=1.0\text{k}\Omega$		2.0	mA
V_{GT}	$V_D=6.0\text{V}, R_L=100\Omega$		0.8	V
V_{TM}	$I_{TM}=1.0\text{A}, t_p=380\mu\text{s}$		1.5	V

R0 (11-December 2008)

SILICON CONTROLLED RECTIFIER
1.6 AMPS, 25 THRU 400 VOLTS

TO-39 CASE - MECHANICAL OUTLINE



DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A (DIA)	0.335	0.370	8.51	9.40
B (DIA)	0.315	0.335	8.00	8.51
C	-	0.040	-	1.02
D	0.240	0.260	6.10	6.60
E	0.500	-	12.70	-
F (DIA)	0.016	0.021	0.41	0.53
G (DIA)	0.200		5.08	
H	0.100		2.54	
I	0.028	0.034	0.71	0.86
J	0.029	0.045	0.74	1.14

TO-39 (REV: R1)

LEAD CODE:

- 1) CATHODE
- 2) GATE
- 3) ANODE (case)

MARKING: FULL PART NUMBER

R0 (11-December 2008)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms