

EX-XR9

M

DRAWING
NUMBER

ISSUE
10

REPLACES

PR-1513

RELEASE NO.

27AUG10

CMH

CHECK

70

CON

4

ROB

CHECK

26APR05

AK

CHECK

70

MB S


20 OCT 70

REVISIONS

A	CO29865	RER	14 DEC 71
B	CO31559	RER	13 FEB 73
C	CO58380	CSH	9 NOV 85
D	CO61381	DAW	22 APR 87
E	CO63239	YLB	21 MAR 88
F	CO73019	MAM	19 SEP 92
G	0010213	BM	21 DEC 04
H	0012750	DVM	26 APR 05
J	0068804	MBN	27AUG10

RASTER
FO-80378-003

DRAWN



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS (AT .688 LEVER LENGTH)	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE --- 1 3/4 LB MAX	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
PRETRAVEL --- .097 MAX (8°)	SINGLE POLE DOUBLE THROW MAINTAINED CONTACT	UNLESS OTHERWISE NOTED
DO NOT OVERTRAVEL MORE THAN --- 90°		DIMENSIONS ARE IN INCHES
RESET CHARACTERISTICS (COUNTER CLOCKWISE ROTATION)		TOLERANCES ARE:
OPERATING FORCE --- 1 3/4 LB MAX	-L96- 15 A-125, 250, OR 480 VAC	ONE PLACE (.0) ±.030
PRETRAVEL --- .097 MAX (8°)	1/2 A-125 VDC; 1/4 A-250 VDC	TWO PLACE (.00) ±.015
OVERTRAVEL --- .013 MIN (1°)	1/8 HP-125 VAC; 1/4 HP-250 VAC	THREE PLACE (.000) ±.005
SWITCH BASIC REPLACEMENT - BZ-RX63-NT		ANGLES
		WEIGHT

