molex



Part Number : 1202530396
Product Description : Contrinex Inductive Sensor, M18 Housing, 8mm Operating Distance, Embeddable, PNP, NO, 4-pin M12 Connector, 63.5mm Housing Length
Series Number : 120253
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AS-623-M18-002

Obsolete

Documents and Resources

Specifications

1202530390-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M18 Housing, 8mm Operating Distance, Embeddable, PNP, NO, 4-pin M12 Connector, 63.5mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130066612

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 1500 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	63.50mm
Material - Housing	Nickel Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Embeddable
Net Weight	344.000/g
Operating Distance	8mm
Output	NO

Obsolete

Downloaded from Arrow.com.

Sensor Housing Size	M18
Temperature Range - Operating	-25° to +70°C

Obsolete

Downloaded from Arrow.com.