

Part Number : [1301070031](#)

Product Description : Super-Safeway Assembled Rubber Stringlight 200W 14/3 SOOW 1.52m (5.0') Lead with Guard 3.04m (10.0'), Overall Length 30.48m (100.0')

Series Number : 130107

Status : Obsolete

Product Category : Lamps and Lights

Engineering Part Number : 310143



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130107
Description	Super-Safeway Assembled Rubber Stringlight 200W 14/3 SOOW 1.52m (5.0') Lead with Guard 3.04m (10.0'), Overall Length 30.48m (100.0')
Component Type	PCB Header
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Super-Safeway
Type	String Lights
UPC	78678879627

Agency

CSA	LR85374
-----	---------

Electrical

Current - Maximum per Contact	1.5A
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	N/A
Cord Type - Primary	14/3 SOOW
Depth	46.48mm (1.830")

Durability (mating cycles max)	10
Duty	Industrial
Gender	Male
Glow-Wire Capable	No
Guard Included	Yes
Guard Type	Steel
Height	101.60mm (4.000")
Lamp Type	A21
Length	30.48m (100.0')
Lock to Mating Part	Yes
Material - Guard	#8 Gauge Zinc-plated Steel
Material - Plating Mating	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Mounting Style	Stringer
Number of Rows	1
Orientation	Vertical
Outlet	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.20mm
Pitch - Termination Interface	1.20mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Polarized to Mating Part	Yes
Socket Construction	Assembled
Temperature Range - Operating	-40° to +105°C

This document was generated on May 20, 2026