

TINA

Ø16.1 mm TIR-lenses for linear lighting, museums, reading lights, compact torches and head lamps compatible with up to 3535 size LED packages

TINA is a versatile family of single Ø16.1 mm lenses consisting of TINA, TINA2 and TINA3 subfamilies. All subfamilies have the same dimensions and come preassembled in lightweight, durable holders - available with or without pins at distance of 8.6 or 6.6 mm - with fastening tape that makes their installation fast and easy. TINA family has a wide selection of beams from narrow to wide flood.


TINA3

Low-profile variant with wider beams for low- and high-bay lighting. Available with a black or white holder, with or without pins. Pin distance 8.6 mm.



PRODUCTS:


CA13044_TINA3-OO



Dimensions: 16.1 mm x 16.1 mm
Height: 7.29 mm

~60° + 40° oval beam. Assembly with holder and installation tape.


FA11825_TINA3-WW



Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~55° wide beam optimized for CREE XP-E. Assembly with holder, installation tape and location pins.

FA11902_TINA3-W




Dimensions: 16.1 mm x 16.1 mm
Height: 7.30 mm

~40° wide beam optimized for CREE XP-E. Assembly with holder, installation tape and location pins.

PRODUCTS:


FA11905_TINA3-S



Dimensions: 16.1 mm x 16.1 mm
Height: 11.40 mm

~13° spot beam optimized for CREE
XP-E. Assembly with holder, installation
tape and location pins.


CA12428_TINA3-WWW



Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~70° wide beam. Assembly with holder,
installation tape and location pins.


CA13043_TINA3-W



Dimensions: 16.1 mm x 16.1 mm
Height: 7.29 mm

~40° wide beam. Assembly with holder
and installation tape.


FA11824_TINA3-W



Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~40° wide beam optimized for CREE
XP-E. Assembly with holder, installation
tape and location pins.


FA11870_TINA3-OO



Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~60° + 40° oval beam optimized for
CREE XP-E. Assembly with holder,
installation tape and location pins.

FA11904_TINA3-WWW




Dimensions: 16.1 mm x 16.1 mm
Height: 7.00 mm

~70° wide beam optimized for CREE
XP-E. Assembly with holder, installation
tape and location pins.

PRODUCTS:


CA12427_TINA3-WW



Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~55° wide beam. Assembly with holder, installation tape and location pins.


CA12892_TINA3-WW



Dimensions: 16.1 mm x 16.1 mm
Height: 7.29 mm

~55° wide beam. Assembly with holder and installation tape.


CA13045_TINA3-WWW



Dimensions: 16.1 mm x 16.1 mm
Height: 7.29 mm

~70° very wide beam. Assembly with holder and installation tape.


FA11826_TINA3-WWW



Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~70° wide beam optimized for CREE XP-E. Assembly with holder, installation tape and location pins.


FA11903_TINA3-WW



Dimensions: 16.1 mm x 16.1 mm
Height: 7.10 mm

~55° wide beam optimized for CREE XP-E. Assembly with holder, installation tape and location pins.

CA12426_TINA3-W




Dimensions: 16.1 mm x 16.1 mm
Height: 6.90 mm

~40° wide beam. Assembly with holder, installation tape and location pins.

PRODUCTS:

CA12429_TINA3-OO-90



Dimensions: 16.1 mm x 16.1 mm

Height: 6.90 mm

~60° + 40° oval beam. Assembly with
holder, installation tape and location pins.

Pin position rotated 90°.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)