

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		PER ECO-18-020143	31DEC2018	MY	GF
B		REVISED PER ECO-20-004723	03APR2020	REH	GF

D

C

B





A

D

C

B

A



1 LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -6): -1 SHOWN.



- TE PN
- LENGTH - CABLE GAGE
- SERIAL NUMBER:
INCLUDES PN, MANUFACTURING LOCATION, AND DATE CODE
- SERIAL NUMBER BARCODE - CODE 39
- COUNTRY OF ORIGIN

9 LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -44): -41 SHOWN.




- TE PN
- LENGTH - CABLE GAGE
- SERIAL NUMBER:
INCLUDES PN, MANUFACTURING LOCATION, AND DATE CODE
- SERIAL NUMBER BARCODE - CODE 39
- COUNTRY OF ORIGIN

10 NO SLEEVING REQUIRED FOR 0.5M LENGTH(2333801-1 AND 4-2333801-1).


- SEE SHEET 2 FOR WIRING SCHEMATIC.
- PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
- CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAMMING.

5 LABEL INFORMATION:



LETTER "A"

6 LABEL INFORMATION:



LETTER "B"

- TEST IN ACCORDANCE WITH IEEE802.3bj.
- DASH NUMBER 41 THRU 44 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

8	30	1000±25	2000 +80/-0	4-2333801-4
	30	500±25	1500 +50/-0	4-2333801-3
	30	500±25	1000 +50/-0	4-2333801-2
	30	250±25	500 +50/-0	4-2333801-1
7	30	1000±25	3000 +80/-0	2333801-6
	30	1000±25	2500 +80/-0	2333801-5
	30	1000±25	2000 +80/-0	2333801-4
	30	500±25	1500 +50/-0	2333801-3
	30	500±25	1000 +50/-0	2333801-2
	30	250±25	500 +50/-0	2333801-1
STANDARD	GAGE	"L2" mm	"L1" mm	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. YI 05MAY2018	TE Connectivity	
DIMENSIONS:		CHK G. FRANKLIN 05MAY2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G. FRANKLIN 05MAY2018	NAME	
	0 PLC ±	PRODUCT SPEC	CABLE ASSEMBLY, QSFP TO (2) QSFP 25GIG, 30AWG	
	1 PLC ±	APPLICATION SPEC		
	2 PLC ±	WEIGHT		
	3 PLC ±	CUSTOMER DRAWING		
MATERIAL	FINISH	SIZE	CAGE CODE	DRAWING NO
-	-	A	00779	C=2333801
-	-	SCALE	5:1	SHEET 1 OF 2
		REV	B	

