


Leaded Platinum Temperature Sensor



PTL Temperature Sensors are the perfect choice for the most fields of modern electronics. The highly controlled platinum thin film manufacturing process guarantees an outstanding stability of temperature characteristics. Typical applications include temperature measurement in process controls in industrial electronics, and precise temperature measurement in medical equipment.

FEATURES

- Advanced platinum thin film technology
- Standardized according IEC 60751
- Outstanding stability of temperature characteristics
- Short reaction times down to $t_{0,9} \leq 8$ s
- 3 ceramic body sizes available
- Radial terminations

APPLICATIONS

Temperature measurement and control in

- Industrial electronics
- Medical electronics

TECHNICAL SPECIFICATIONS

DESCRIPTION		PTL 1112	PTL 1222	PTL 1252
Resistance values R_0 at 0 °C ⁽¹⁾		100 Ω, 500 Ω, 1000 Ω	100 Ω, 500 Ω, 1000 Ω	100 Ω, 500 Ω, 1000 Ω, 10 000 Ω
Temperature coefficient (0 °C to + 100 °C)		+ 3850 ppm/K		
Tolerance class		F0.15, F0.3 ⁽¹⁾		
Temperature range		- 50 °C up to + 550 °C ⁽¹⁾		
Long term stability $\Delta R_0/R_0$ (250 h at UCT)		< ± 0.1 %		
Insulation resistance		> 10 MΩ		
Measurement current $I_{mea.}$ (DC) ⁽³⁾		Up to 1.0 mA for 100 Ω Up to 0.4 mA for 500 Ω Up to 0.3 mA for 1 kΩ Up to 0.1 mA for 10 kΩ		
Self-heating ⁽²⁾	Flowing air (v = 3.0 m/s)	≤ 0.25 K/mW	≤ 0.2 K/mW	≤ 0.17 K/mW
	Still air (v = 1.0 m/s)	≈ 0.6 K/mW	≈ 0.4 K/mW	≈ 0.35 K/mW
Thermal response time ⁽²⁾	Flowing air (v = 3.0 m/s)	t _{0,5} ≤ 2.5 s	t _{0,5} ≤ 3 s	t _{0,5} ≤ 5 s
		t _{0,9} ≤ 8 s	t _{0,9} ≤ 10 s	t _{0,9} ≤ 15 s
Material of leads		Platinum clad Ni ⁽¹⁾		
Length of leads		10 mm ⁽¹⁾		
Diameter of leads		0.2 mm ⁽¹⁾		


Notes

⁽¹⁾ Customized solutions on request, tolerance class F0.15 up to 300 °C, class F0.3 up to 500 °C

⁽²⁾ Valid for sensor element only

⁽³⁾ Indicated measurement currents can be applied continuously with self-heating effect of less than 0.1 °C at 0 °C in still air

DIMENSIONS in millimeters



DIMENSIONS - PTL sensor type, relevant physical dimensions

TYPE	H ₁	H ₂	L	W	Ø d	I	F	S	MASS (mg)
PTL 1112	1.0 ± 0.25	0.4 ± 0.05	1.6 ± 0.2	1.25 ± 0.2	0.2 ± 0.02	10.0 ± 1.0	0.55	0.35	16
PTL 1222	1.0 ± 0.25	0.4 ± 0.05	2.3 ± 0.2	2.0 ± 0.3	0.2 ± 0.02	10.0 ± 1.0	0.90	0.55	24
PTL 1252	1.0 ± 0.25	0.4 ± 0.05	5.0 ± 0.2	2.0 ± 0.3	0.2 ± 0.02	10.0 ± 1.0	0.90	0.55	36

PRODUCTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of platinum is deposited on a high grade ceramic body (96 % Al₂O₃). The sensor-elements are covered by a protective coating designed for electrical, mechanical and climatic protection.

QUALITY

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual sensors. Only accepted products are laid directly into the waffle trays. The resistance values and tolerances according to DIN EN 60751 are given for the device including the standard leads. Any additional wiring will change resistance values for the total setup.

ASSEMBLY

The Pt-sensors are suitable for all standard assembly processes like crimping, soldering, brazing and welding (LASER- or resistive welding).

The parameters of the assembly process should be chosen in accordance with the used wire material. It is recommended to verify the parameters by pre-testing.

The assembly process of the sensor should be in compliance with the following guidelines and recommendations:

- Fixation of only one lead during assembly
- Tensile forces parallel to the leads < 5 N
- Avoiding of large temperature gradients between the welding region and the sensor during assembly, e.g. by using a cooled clamp with a good thermal conductivity
- Radius of curvature of the leads > 0.3 mm

- Curvature or torsion strain > 3 mm away from the sensor element
- After assembly we recommend to fix the leads in the welded region with a strain relief

ENVIRONMENTAL CONDITIONS

Unprotected sensor-elements are usable under dry environmental conditions only. Platinum-plated nickel leads enable the usage in applications with ambient temperatures up to 550 °C. The environment of the sensor application should be without any corrosive substances (e.g. potassium hydroxide or hydrogen fluoride) or other contaminants which could affect the sensor, especially shifting the temperature coefficient of the sensor. This has also to be considered during the assembly process.

DIRECTIVES

All products comply with the CEFIC-EECA-EICTA list of legal restrictions on hazardous substances.

This includes full compatibility with the following directives:

- 2000/53/EC End of Vehicle Life Directive (ELV)
- 2000/53/EC Annex II to End of Vehicle Life Directive (ELV II)
- 2002/95/EC Restriction of the use of Hazardous Substances Directive (RoHS)
- 2002/96/EC Waste Electrical and Electronic Equipment Directive (WEEE)

APPROVALS

The Pt-sensors are tested in accordance with **IEC 60751/ DIN EN 60751**.



PART NUMBER AND PRODUCT DESCRIPTION ⁽¹⁾

PART NUMBER ⁽²⁾: PTL122201B1K00KU00

P	T	L	1	2	2	2	0	1	B	1	K	0	0	K	U	0	0
TYPE			TYPE CODE				SPECIAL CHARACTER		TOLERANCE CLASS		RESISTANCE VALUE			PACKAGING ⁽³⁾		SPECIAL	
3 digits			4 digits				1 digit		2 digits		4 digits			2 digits		2 digits	
PTL = Platinum Temperature Sensor Leaded			1112 1222 1252				0 = Neutral		1A = Class F0.15 1B = Class F0.3		100R = 100 Ω 500R = 500 Ω 1K00 = 1000 Ω 10K0 = 10 k Ω			Waffles in a box KU K1		00 = Standard	

PRODUCT DESCRIPTION ⁽⁴⁾: PTL 1222 -B KU 1K0

PTL	1222	-B	KU	1K0
TYPE	TYPE CODE	TOLERANCE CLASS	PACKAGING ⁽³⁾	RESISTANCE VALUE
PTL = Platinum Temperature Sensor Leaded	1112 1222 1252	A = Class F0.15 B = Class F0.3	Waffles in a box KU K1	100R = 100 Ω 500R = 500 Ω 1K0 = 1000 Ω 10K0 = 10 000 Ω

Notes

⁽¹⁾ Products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

⁽²⁾ The part number is shown to facilitate the introduction of unified part numbering system

⁽³⁾ Please refer to table PACKAGING

⁽⁴⁾ We recommend that the production description is used to minimize the possibility of errors in order handling

PACKAGING

MODEL	WAFFLE PACK	
	PIECES/WAFFLES IN A BOX	CODE
PTL	100	KU
	1000	K1

FUNCTIONAL PERFORMANCE

The temperature resistance relationships of the PTL series follow different equations:

for the temperature range from - 50 °C up to 0 °C:

$$R_T = R_0 \times (1 + A \times T + B \times T^2 + C \times (T - 100 \text{ °C}) \times T^3)$$

and for the temperature range from 0 °C up to + 550 °C:

$$R_T = R_0 \times (1 + A \times T + B \times T^2)$$

R_T : Resistance as a function of temperature

R_0 : Nominal resistance value at 0 °C

T : Temperature in °C

According to IEC 60751/DIN EN 60751 the values of the coefficients are:

$$A = 3.9083 \times 10^{-3} \text{ °C}^{-1}$$

$$B = - 5.775 \times 10^{-7} \text{ °C}^{-2}$$

$$C = - 4.183 \times 10^{-12} \text{ °C}^{-4}$$

The temperature tolerances values of the PTL series are classified by the following equation:


$$\text{Class F0.15: } \Delta T_{F0.15} = \pm (0.15 + 0.002 \times |T|)$$

(valid from - 50 °C to 300 °C)


$$\text{Class F0.3: } \Delta T_{F0.30} = \pm (0.30 + 0.005 \times |T|)$$

(valid from - 50 °C to 500 °C)


NOMINAL RESISTANCE VALUE						
TEMPERATURE (°C)	$R_0 = 100 \text{ } \Omega$	$R_0 = 500 \text{ } \Omega$	$R_0 = 1000 \text{ } \Omega$	$R_0 = 10\,000 \text{ } \Omega$	CLASS F0.15	CLASS F0.30
	NOMINAL RESISTANCE (Ω)	NOMINAL RESISTANCE (Ω)	NOMINAL RESISTANCE (Ω)	NOMINAL RESISTANCE (Ω)	TOLERANCE (K)	TOLERANCE (K)
- 50	80.306	401.53	803.06	8030.6	± 0.25	± 0.55
- 25	90.192	450.96	901.92	9019.2	± 0.20	± 0.43
0	100	500	1000	10 000	± 0.15	± 0.30
25	109.73	548.67	1097.3	10 973	± 0.20	± 0.43
50	119.40	596.99	1194.0	11 940	± 0.25	± 0.55
75	128.99	644.94	1289.9	12 899	± 0.30	± 0.68
100	138.51	692.53	1385.1	13 851	± 0.35	± 0.80
125	147.95	739.76	1479.5	14 795	± 0.40	± 0.93
150	157.33	786.63	1573.3	15 733	± 0.45	± 1.05
175	166.63	833.13	1666.3	16 663	± 0.50	± 1.18
200	175.86	879.28	1758.6	17 586	± 0.55	± 1.30
225	185.01	925.07	1850.1	18 501	± 0.60	± 1.43
250	194.10	970.49	1941.0	19 410	± 0.65	± 1.55
275	203.11	1015.6	2031.1	20 311	± 0.70	± 1.68
300	212.05	1060.3	2120.5	21 205	± 0.75	± 1.80
325	220.92	1104.6	2209.2	22 092		± 1.93
350	229.72	1148.6	2297.2	22 972		± 2.05
375	238.44	1192.2	2384.4	23 844		± 2.18
400	247.09	1235.5	2470.9	24 709		± 2.30
425	255.67	1278.4	2556.7	25 567		± 2.43
450	264.18	1320.9	2641.8	26 418		± 2.55
475	272.61	1363.1	2726.1	27 261		± 2.68
500	280.98	1404.9	2809.8	28 098		± 2.80
525	289.27	1446.3	2892.7	28 927		± 2.93
550	297.49	1487.4	2974.9	29 749		



Tolerance for Class F0.15



Tolerance for Class F0.3





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.